



# **MD24-12**

## **Mini Directional Antenna**

# MINI DIRECTIONAL ANTENNA, 2400 TO 2483 MHZ OPERATION

The 2.4 GHz mini directional antennas are a sub-compact antenna for the most demanding client applications. The antennas offer high gain in an ultra-small, aesthetically pleasing package. These are constructed of gray color UV ABS plastic with aluminum backplate and a stainless steel mounting bracket.

The antenna can be used in horizontal or vertical polarization by making a change to the bracket mounting. The stainless steel bracket affords +/- 15° tilt adjustment. The compact, low visual impact attractive styling blends well in almost any application. The antenna comes with an integral N female connector standard.

#### **FEATURES AND BENEFITS**

- 11 dBi gain in a mini directional antenna
- · Rugged and weatherproof
- Ultra low wind loading and ultra low visual impact
- · Vertical or horizontal polarization
- Type N female connector
- · Stainless steel bracket and hardware

#### **APPLICATIONS**

- 2.4 GHz wireless LAN applications
- 802.11b/g client antennas
- WiMAX


SPECIFICATIONS	
Frequency range	2400 to 2483 MHz
Gain	11 dBi
Horizontal beamwidth	65°
Vertical beamwidth	34°
Front-to-back	25 dB
Input return loss (S11)	-14 dB
VSWR	1.5:1
Impedance	50 ohm
Input power	100 W
Operating temperature	-40°C to +70°C

SPECIFICATIONS	
Pole size	1 to 1.66 in (25 mm to 39 mm)
Weight	13.5 oz (383 g)
Dimension (W x L x H)	4 x 4 x 4 in(102 x 102 x 102 mm)


## **SYSTEM ORDERING**

MD24-12 2.4 GHz 11 dBi Mini Directional Antenna

#### **ANTENNA PATTERNS**



Horizontal plane 2400 MHz



Elevation plane 2400 MHz

#### TE TECHNICAL SUPPORT CENTER

USA: +1 (800) 522-6752 +1 (905) 475-6222 Canada: Mexico: +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 +44 (0) 800-267666 UK: +33 (0) 1-3420-8686 France: Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

#### te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE product is installed. Useful lifetime of the original end product may vary but is not to exceed five (5) years from the original date of the end product purchase.

©2021 TE Connectivity. All Rights Reserved.

10/21 Original

