



## UM/L Universal Antenna Mount

The UM/L universal antenna mounting systems consist of a universal bracket and choice of 2 different length mounting tube for the most demanding customer premises antenna mounting applications. The construction is better than many of these type of mounts which are only light gauge painted steel. TE Connectivity's mounts are heavy gauge steel which goes through a galvanization (plating) process and then are powder coat painted for extra protection from the elements. Fasteners used are stainless steel. The mounting tubes have 2 sets of holes to give maximum angular flexibility during installations. The mounting systems feature a universal mounting bracket with a full 90 degrees of tilt which allows for greater versatility when dealing with the variety of installation challenges found at customer sites. Their low profile and attractive styling make it ideal for installations on various styles of buildings and in all neighborhoods, including upscale neighborhoods.

### FEATURES AND BENEFITS


- Attractive styling
- Galvanized steel with grey powder coat paint
- Full 90 degree tilt adjustment
- 1.5" heavy duty steel tube for greater strength
- Extremely versatile
- Supports 150Lbs. load in both axis
- 2 Sets of holes in tube for more angular flexibility
- Base accepts our standard U-Bolts for pole mounting

### APPLICATIONS

- Customer premises equipment
- Roof or wall mounting
- Under-eave mounting
- Interior or exterior

PART NUMBER	DESCRIPTION
UM	Universal Mount
UML	Universal Mount, Extra Long
UM-UB	U-Bolt Kit for Pole Mount

## MECHANICAL DRAWING



### Notes:

All dimensions are in inches.

Heavy duty tube diameter: 1.5". 90 degree adjustable tilt.

Mounting flange width: 6".

Material: Galvanized steel, grey epoxy power coat paint All shipments F.O.B Schaumburg, IL 60173

## TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

## te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, complete, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE EXPRESSLY DISCLAIMS ALL IMPLIED WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. In no event will TE be liable for any direct, indirect, incidental, special or consequential damages arising from or related to recipient's use of the information. It is the sole responsibility of recipient of this information to verify the results of this information using their engineering and product environment. Recipient assumes any and all risks associated with the use of the information. Antenna performance may vary. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements.

©2025 TE Connectivity. All Rights Reserved.

05/25 Original