





B1360W

Wide Band Mobile Load Coil Antenna 136-174 MHz

Laird Connectivity's ongoing commitment to refinement in mechanical and electrical design has resulted in the most technically advanced mobile load coil antennas on the market. Exclusive features such as stainless-steel whips, housings constructed with ABS material injected molded around a solid brass insert, and gold-plated push pin contacts make Laird Connectivity the obvious choice for quality and long-lasting value for demanding mobile radio communications.

FEATURES AND BENEFITS

- High performance wide band mobile antenna
- Special UV-treated radome, resists sun damage

APPLICATIONS

- Public safety
- Transportation
- Utility
- Military mobile

•	Easy	installation	with	optional	NMO	mounts

• 100% tested on a network analyzer

ELECTRICAL SPECIFICATION			
Model Name	B1360W		
Operating Frequency (MHz)	136-174		
Number of Ports	1 (VHF)		
Center Frequency (MHz)	155		
Gain	Unity		
Pattern	Omnidirectional		
VSWR	≤ 2.0:1		
Nominal Impedance (Ohms)	50		
Max Power - Ambient 25°C (W)	100		
Polarization	Vertical		

MECHANICAL SPECIFICATIONS			
Length – cm (inches)	~49.4 (~19.5)		
Diameter – mm (inches)	36.58 (1.44)		
Weight - kg (oz.)	0.268 (9.44)		
Termination	1-1/8" - 18 thread (NMO) mounts		
Mounting Options (sold separately)	3/4" or 3/8" NMO magnetic or trunk mount		
Radiator	17-7ph straight stainless steel		
Shock Spring	302 stainless steel		
Base Housing Material	Molded ABS		
Noise Suppressor (sold separately)	Blackhawk NS1535		

ENVIRONMENTAL SPECIFICATIONS			
Operating Environment (Indoor or Outdoor)	Outdoor		
Wind Resistance - sq. ft.	0.049		
Material Substance Compliance	RoHS		


CONFIGURATION

PART NUMBER	DESCRIPTION
B1360W	Chrome B-coil wide band antenna
BB1360W	Black B-coil wide band antenna
B1360WS	Chrome B-coil wide band antenna w/ spring
BB1360WS	Black B-coil wide band antenna w/ spring


RADIATION PATTERNS

154 MHz

Azimuth Plot



Elevation Plot



VSWR PLOT AT 136-174 MHZ



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31(0)73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warrantied to exceed one (1) year from the original date of the end product purchase.

©2022 TE Connectivity. All Rights Reserved.

08/22 Original

DATA AND DEVICES / B1360W

