



FG1480

Omnidirectional Antennas 148-152 MHz

FEATURES AND BENEFITS

- High performance
- Easy installation with optional FM2
- N Female industry standard connector
- Special UV-treated radome - resists sun damage
- 100% tested on a network analyzer

ELECTRICAL SPECIFICATIONS

Model Name	FG1480
Operating Frequency (MHz)	148-152
VSWR - Max	< 2.0:1
Gain (dBi)	0
Nominal Impedance (Ohms)	50
Max Power - Ambient 25°C (W)	100
Polarization	Vertical
Pattern	Omnidirectional
Elevation Plane 3 dB Beamwidth Port 1	120°
Azimuth Plane 3 dB Beamwidth Port 1	360°

MECHANICAL SPECIFICATIONS

Dimensions - H x D - cm (inches)	185.4 x 3.3 (73.0 x 1.31)
Weight - kg (lbs.)	< 1.81 (< 4.0)
Cable Type	None
Mounting	FM2 mounting kit (sold separately)
Lightning Protection	LABH350NN (sold separately)



***FM2 MOUNTING KIT
(SOLD SEPARATELY)***




***LABH350NN (SOLD
SEPARATELY)***

ENVIRONMENTAL SPECIFICATIONS

Rated Wind Velocity – km/hr (mph)	210 (125)
Rated Wind Velocity (w/ 0.5” radial ice) – km/hr (mph)	137 (85)
Lateral Thrust @ 125 mph Wind Velocity – kg (lbs.)	26 (57)
Wind Resistance – sq. km (sq. ft.)	6.17 (.6641)
Material Substance Compliance	RoHS

RADIATION PATTERN



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, complete, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE EXPRESSLY DISCLAIMS ALL IMPLIED WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. In no event will TE be liable for any direct, indirect, incidental, special or consequential damages arising from or related to recipient's use of the information. It is the sole responsibility of recipient of this information to verify the results of this information using their engineering and product environment. Recipient assumes any and all risks associated with the use of the information. Antenna performance may vary. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements.

©2025 TE Connectivity. All Rights Reserved.

05/25 Original