



HCF69273xN

Omni-directional Antenna 698-960 MHz/1690-2700 MHz

This TE LTE HCF69273 omni-directional antenna is a tough low-profile antenna for outdoor or indoor applications. This antenna provides frequency agility, low visibility, wide bandwidth and a low angle radiation pattern that is superior to traditional gain antennas in most applications. The HCF69273 antenna is available in various industrystandard mounting configurations including a threaded permanent stud mount model for vandal resistant mounting on brackets, panels, ceilings, or any other kind of housing.

FEATURES AND BENEFITS

- Multi-band operation: 698-960 MHz/1690-2700 MHz
- Meets IP67 protection rating for dust tight seal and temporary water immersion
- Permanent mount with coaxial pigtail is ideal for radios within a metal enclosure
- Conformance to RoHS

ELECTRICAL SPECIFICATIONS

Operating Frequency (MHz)	698-824	824-894	880-960	1690-1880	1850-1990	1920-2170	2300-2500	2500-2700
Peak Gain - Avg (dBi)	1.0	1.2	1.0	2.8	3.1	3.3	3.3	3.4
Peak Gain - Max (dBi)	1.5	1.2	1.2	3.3	3.4	3.6	3.5	3.8
VSWR - Avg	<1.8	<1.8	<2.1	<1.4	<1.6	<1.5	<1.3	<1.6
VSWR - Max	<2.6:1				<2.0:1			
Nominal Impedance (Ohms)	50							
Max Power - Ambient 25°C (W)	10							
Polarization	Vertical							
Azimuth 3 dB Beamwidth	360° (Omnidirectional)							

MECHANICAL SPECIFICATIONS

Dimensions - height x diameter - mm (inches)	80.0 x 37.0 (3.2 x 1.5)
Weight - kg (lbs.)	0.10 (0.22)
Radome	PC, Lexan EXL9330, UV Resistant, UL94 V-0
Antenna Color	Black/White
Installation Torque (Nm)	4-6

ENVIRONMENTAL SPECIFICATIONS

Operating Environment (Indoor or Outdoor)	Indoor and Outdoor
Operating Temperature – °C (°F)	-30 to +70 (-22 to +158)
Storage Temperature – °C (°F)	-40 to +85 (-40 to +185)
Ingress Protection Rating	IP67
Material Substance Compliance	RoHS

CONFIGURATION

PART NUMBER	CABLE TYPE	CABLE LENGTH	CONNECTOR	COLOR
HCF69273BN-60A	Ultralink 092463	60.8 cm (24 in.)	SMA Male	Black
HCF69273WN-60A	Ultralink 092463	60.8 cm (24 in.)	SMA Male	White

PACKAGED DIMENSIONS	CARTON	AIR PALLET	OCEAN PALLET
Number of Antennas	50	900	1,200
Height – cm (in.)	30.1 (11.85)	104.0 (41.0)	135.0 (53.15)
Length – cm (in.)	26.6 (10.47)	120.0 (47.24)	120.0 (47.24)
Width – cm (in.)	52.6 (20.71)	80.0 (31.5)	80.0 (31.5)
Shipping Weight – kg (lb.)	7.325 (16.15)	141.85 (312.73)	185.8 (409.62)

PACKAGING INFORMATION




FIGURE 1: HCF69273XN MECHANICAL DRAWING

MOUNTING OPTIONS






FIGURE 2: HCF69273M3 MOUNTING

RADIATION PATTERNS


698 MHz




824 MHz




960 MHz




1690 MHz




1950 MHz




2170 MHz



2412 MHz



2700 MHz



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, complete, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE EXPRESSLY DISCLAIMS ALL IMPLIED WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. In no event will TE be liable for any direct, indirect, incidental, special or consequential damages arising from or related to recipient's use of the information. It is the sole responsibility of recipient of this information to verify the results of this information using their engineering and product environment. Recipient assumes any and all risks associated with the use of the information. Antenna performance may vary. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements.

©2025 TE Connectivity. All Rights Reserved.

05/25 Original