



IN7-3RD

700 MHz Rubber Duck Antenna

700 MHZ APXTENDER OMNIDIRECTIONAL ANTENNA

The 3 dBi APXtender Indoor Rubber Duck Omnidirectional Antenna is a high gain antenna for fixed or portable wireless equipment operating in the 700 MHz frequency range. The antenna features a 360 horizontal transmission pattern and a 50 vertical transmission pattern. The transmit/receive element can be tilted in relation to the base to direct signal where it is needed. The antennas are available in various connectors to fit most wireless radio equipment.

FEATURES

- 3 dBi gain 700 MHz omnidirectional indoor antenna
- Extends range of 700 MHz wireless access points or wireless bridges


MARKETS

- 700 MHz wireless access points
- 700 MHz wireless client bridges
- 700 MHz wireless routers
- OEM wireless equipment
- WiMAX

PARAMETER	MIN	TYP	MAX	UNITS
Frequency Range	698		806	MHz
Gain		3		DBI
VSWR		1.5:1		
Impedance		50		OHM
Input Power			10	W
Operating Temperature	-10		+60	C
Weight		1.3 (37)		oz (gr)
Dimension		6.2 x 0.6 D (157.5 x 15.2 D)		in (mm)

ORDERING INFO

IN7-3RD-SMA	3 dBi 700 Mhz APXtender	SMA Male Connector
IN7-3RD-RSMA	3 dBi 700 Mhz APXtender	Reverse Polarity SMA Connector
IN7-3RD-RTNC	3 dBi 700 Mhz APXtender	Reverse Polarity TNC Connector



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, complete, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE EXPRESSLY DISCLAIMS ALL IMPLIED WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. In no event will TE be liable for any direct, indirect, incidental, special or consequential damages arising from or related to recipient's use of the information. It is the sole responsibility of recipient of this information to verify the results of this information using their engineering and product environment. Recipient assumes any and all risks associated with the use of the information. Antenna performance may vary. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements.

©2025 TE Connectivity. All Rights Reserved.

05/25 Original