






COIL: @ 25°C
 RESISTANCE 75 OHMS ± 10%
 NOMINAL VOLTAGE 12.0 VDC
 MUST OPERATE 6.5 VDC
 MUST RELEASE 0.9 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 50 g's 11 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 10 MS MAX.
 CONTACT BOUNCE 5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 10 AMPS 28 VDC
 5 AMPS 115 VAC/400 Hz 1 OR 3 PHASE
 RESISTIVE 100,000 OPERATIONS

DR. R.B. 8/5/97

CK. 8/5/97



COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. C. I. I.
 CUST. NO. STD.

TYPE '07' RELAY

B07D0035BB1