

923 Extension

speedtec - ready

9-pin EMC - Shielding Earth-to-Housing Connection according to VDE 0627 Anti-vibration o-ring

B KU A 145 NN 00 59 0200 000 B K A 145 N 00 59 0200 000



Contact Arrangement mating view



Technical Data number of pins

power signal temperature range clamping range protection type 9 4 (3+PE) 5 -20 °C to 130 °C Ø 14.0 mm to Ø 17.0 mm when connected IP 66/67

signal

2500 V

max. 7 A* 250 V (AC/DC)

Electrical Data rated current rated voltage rated insulation voltage (L-L)

6000 V

3

power

max. 30 A* 630V (AC/DC)

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

zinc diecast / nickel plated PA 6.6 mod., UL 94/V0

brass / nickel plated

pollution degree over voltage category max. height for operation

III 2000 m

FKM

Material

mating cycles

housing insulation insert seals clamp ring

Contacts (not part of product contents)

Tools (not part of product contents)

© 2018 TE Connectivity


TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the unformation contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference nurnoses only and are subject to change without

in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mali: intercontec@te.com Web: www.intercontec.biz





Main Dimensions Extension *for max. wire cross-section pay attention to the cross-section of used contacts