



## SP6 Coaxial Surge Protectors

### COAXIAL SURGE PROTECTORS

#### DC to 6 GHz Operation

SP6 surge protectors are an integral part of any antenna installation involving the protection of sensitive equipment from surges caused by lightning. The ultra fast discharge design gives quick response to power surges and dumps the excess power safely to ground. Grounding is accomplished via a ground lug terminal or N bulkhead connector. The units have the ability to withstand multiple lightning strikes. The SP6 passes DC voltage so it is also suitable for those systems which pass DC power through the coax such as remote amplifiers. Construction is all plated brass to resist corrosion.

#### FEATURES

- Ultra fast gas discharge < 1KV / usec
- 0.2 dB @ 2.4 GHz, 0.4 dB @ 5 GHz  
max insertion loss
- VSWR better than 1.4:1
- Rugged, lightweight and IPx7  
waterproof
- Bulkhead mount N female connector

#### APPLICATIONS

- Lightning protection for antenna systems
- 900 MHz, 2.4 GHz @ 5 GHz WLAN systems
- WiMAX

PARAMETER	MIN	TYP	MAX	UNITS
Frequency Range	DC	2400	6000	MHz
Insertion Loss	.1	.2	.4	dB
VSWR	1.1 : 1	1.2 : 1	1.4 : 1	
DC Breakdown Voltage		230		V
Impulse Breakdown Voltage (1 KV/uS MAX)		700		V
Impulse Wave Discharge (5 times)		10000		A
Impedance		50		OHM
Insulation Resistance (100 V)	50			
Imput Power			100	W
Operating Temperature	-40		+85	°C
Weight		4.5 (130)		oz (g)
Dimensions (incl connectors)	2.7 x 1.2 x 0.9 (68 x 31 x 23)			in. (mm)
Ingress Protection	IPx7			

## SYSTEM ORDERING

**SP6-230-BFF DC to 6 GHz, bulkhead N female to N female, 230 V surge protector**

**SP6-230-BFM DC to 6 GHz, bulkhead N female to N male, 230 V surge protector**

### TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

### te.com

TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warranted to exceed one (1) year from the original date of the end product purchase.

©2022 TE Connectivity. All Rights Reserved.

08/22 Original