EKM-2050-2D1-5S/U-RTBL Art.-Nr.: BM4822-000 (JOR-88490)




According to DIN VDE 0660-505 DIN 43628

For installation in lighting columns with minimum diameter of 90 mm With door opening minimum 80 x 270 mm With two fuses D01 (E14) up to 16 A With 2 screw caps With 5 sliding terminals Prewired with bars (N, L1, (L3), L2, PE(N)) All metal parts corrosion protected (Ni-plated brass or stainless steel) transparent cover Protection class II (with double or increased insulation) With ingress protection IP 54 For 1 or 2 earth cables 4 mm² - 25 mm² or 3 earth cables 4 mm² - 16 mm² With easy adaptable cable sealing for 1-3 earth cables Ø 19 – 24 mm For 2 luminaire cables 3 x 1,5 mm² - 5 x 2,5 mm² 2 sealing grommets for luminaire cables \emptyset 8 – 14 mm Two additional luminaire cables can be routed towards the bottom of the box Standard Packing size: 1

- 1 DIN rail TS 35

- 2 pcs. series terminals (Cage- Clamp), red and blue for wires up to 2,5 mm2, for connecting and control of DALI- devices

circuit diagram:



]

63

