



Ultra Phantom

Omnidirectional Antenna

TE's unique patented Ultra Phantom® single-band antenna is a rugged low-profile antenna for outdoor or indoor applications. The Ultra Phantom features vertical polarization, low visibility, wide bandwidth and a low angle radiation pattern that is superior to traditional gain antennas in most applications.

The industry standard NMO mounting socket mates with all TE magnetic, trunk lid and whole mounts.

FEATURES AND BENEFITS

- Outperforms 3-dBi whip antennas in many applications
- IP67-rated for harsh environment applications
- U.S. patent numbers 5,977,931 – 6,292,156 and 7,209,096
- RoHS-compliant

APPLICATIONS

- Public safety
- Transportation
- Utilities
- Military mobile
- Fixed radio applications

ELECTRICAL SPECIFICATIONS

Frequency Range	380-512 (see Model and Ordering Information)
VSWR - Avg	≤ 2.5:1
Gain (dBi)	2.0 – 4.1 (see Model and Ordering Information)
Max Power - Ambient 25°C (W)	100
Nominal Impedance (Ohms)	50
Pattern Type	Omnidirectional
Polarization	Vertical

MECHANICAL SPECIFICATIONS

Dimensions - diameter x height - mm (inches)	35.5 x 86.3 (1.4 x 3.4)
Weight - g (lbs.)	163.3 (0.36)
Mounting	NMO
Color	Black or white
Lightning Protection	

ENVIRONMENTAL SPECIFICATIONS


Operating Temperature - °C (°F)	-45 to +85°C (-49 to +185°F)
Storage Temperature - °C (°F)	-50 to +85°C (-58 to +185°F)
Wind Survival - km/hr (mph)	282 (175)
Ingress Protection Rating	IP67
Material Substance Compliance	RoHS

MODEL AND ORDERING INFORMATION


PART NUMBER	FREQUENCY (MHZ)	MAX. GAIN (DBI)	COLOR
UTRA4502S3NB/ UTRA4502S3NW	450-512	4.1	Black/White
UTRA4301S3NB/ UTRA4301S3NW	430-490	3.6	Black/White
UTRA4061S2NB/ UTRA4061S2NW	406-440	2.9	Black/White
UTRA3802S1NB/ UTRA3802S1NW	380-410	2.0	Black/White

RADIATION PATTERNS


450 MHz




430 MHz




406 MHz




380 MHz




512 MHz




490 MHz



440 MHz



410 MHz



TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, TE Connectivity, TE connectivity (logo), and EVERY CONNECTION COUNTS are trademarks owned or licensed by the TE Connectivity plc family of companies. Other product names, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this document, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, complete, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE EXPRESSLY DISCLAIMS ALL IMPLIED WARRANTIES REGARDING THE INFORMATION CONTAINED HEREIN, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. In no event will TE be liable for any direct, indirect, incidental, special or consequential damages arising from or related to recipient's use of the information. It is the sole responsibility of recipient of this information to verify the results of this information using their engineering and product environment. Recipient assumes any and all risks associated with the use of the information. Antenna performance may vary. TE is a component manufacturer, and customer and/or end-user is responsible for all end-use compliance and regulatory requirements.

©2025 TE Connectivity. All Rights Reserved.

05/25 Original