



SUBMERSIBLE Pressure & Temperature Tra

Pressure & Temperature Transmitter AST45PT

Overview

The AST45PT is a combined pressure and temperature transmitter for accurate liquid level measurement.

For pressure ranges from 0-1 to 100 PSI that require a wide range of media compatibility, the AST45PT submersible series is an excellent solution to monitor level and temperature for indoor and outdoor applications.

Benefits

- High Strength Stainless Steel Construction
- No Internal O-rings
- Wide Operating Temperature
- Pressures up to 100 PSI
- Low Static and Thermal Errors
- Unparalleled Price and Performance
- Rugged Design
- New Conduit Fitting at Electrical Connection
- Compatible with Wide Variety of Liquids
- EMI/RFI Protection

Applications

- Ground Water Level Measurement
- Earthen & Concrete Dams
- Liquid Tanks
- Irrigation
- Environmental Sites
- Building Automation Controls
- Waste Water Canals

Environmental Data

Ambient Temperature: 25°C (77°F) (Unless otherwise specified)

Operating Ambient	-40 to 85°C (-40 to 185°F)
Storage	-40 to 100°C (-40 to 212°F)

Shock, Vibration & Ingress Protection (IP)

Standard	Description	Test Value
EN 60067-2-27	Shock Test	500m/s ² , 6ms, half sine-wave, 6 shocks (3/direction), horizontal and vertical axis, 12 total shocks
EN 60068-2-6	Sinusoidal Vibration	5-25 Hz, 2mm, 25-150 Hz, 50m/s, Sweep rate: 1 octave/min, Duration: 24 hours/axis (48 hours total), horizontal and vertical axis
EN 60068-2-64	Random Vibration	10-2000 Hz, vibration level: 0.0314 (m/s ²) ² /Hz, 24 hrs/axis (48 hrs total), 2 directions: horizontal and vertical
IEC 60068-2-32	Drop Test	Drop of 1 meter to floor made of concrete. Dropped twice on the threaded end and two times perpendicular to the threaded end.
IP-68	Ingress Protection	Dust-tight, protected against the effects of continuous immersion in water

Performance

Ambient Temperature: 25°C (77°F) (Unless otherwise specified)

Parameters	MIN	ТҮР	MAX	UNITS	NOTES
Accuracy (Pressure)	-0.25		+0.25	%Span	1
Accuracy (Temperature)	-2.0		+2.0	%TEB	8
Zero Error	-0.5		+0.5	%Span	2
Span Error	-0.5		+0.5	%Span	3
Thermal Error, Zero	-1.5		+1.5	%Span	4
Thermal Error, Span	-1.5		+1.5	%Span	5
Stability (1 year)		±0.25		%Span	
Proof Pressure		2X Rated Pressure		PSI	6
Burst Pressure		5X Rated Pressure		PSI	7
Compensated Temp. Range		0 – 55° (32 to 132°)	0 – 55° (32 to 132°)		

Electrical Data

Model	AST45PT					
Output	4-20mA	1-5V				
Excitation	10-28VDC	10-28VDC				
Output Impedance	> 10k Ω	< 100 Ω				
Current Consumption	-	<10mA				
Output Noise	-	<1mv RMS				
Output Load	0-800Ω	5k Ω Min.				
Reverse Polarity Protection	Yes	Yes				
Sampling Rate	400 Hz	400 Hz				

Notes

1. The maximum deviation from a best fit straight line (BFSL) fitted to the output measured over the pressure range at 25°C. Includes all errors due to pressure

non-linearity, hysteresis, and non-repeatability. Span is the algebraic difference between full scale output and zero pressure offset.

2. The maximum variation from the ideal offset measured at 25°C.

3. The maximum variation from the ideal full-scale span measured at 25°C.

4. The maximum variation of offset within the compensated temperature range relative to 25°C.

5. The maximum variation of full-scale span within the compensated temperature range relative to 25°C.


6. The maximum pressure that can be safely applied to the product tor it to remain in specification once pressure is returned to the operating pressure range.

7. The maximum pressure that can be applied without causing escape of the pressure media.

8. The deviation from a straight line fitted through the compensated temperature end points expressed a percentage of the temperature output range.

Dimensions & Electrical Connection

Unless otherwise specified, all dimensions are in inches



Available Process Connection, Material Configurations & Pressure Codes

316L PSI								
Pressure Range	Pressure Range Code	PSI Unit	Process Connection Code					
Flessure Kalige	Fressure Range Code	r Si Oliit	L					
0 - 1	00001	Р	\checkmark					
0 - 5	00005	Р	\checkmark					
0 - 10	00010	Р	\checkmark					
0 - 15	00015	Р	\checkmark					
0 - 25	00025	Р	\checkmark					
0 - 50	00050	Р	\checkmark					
0 - 100	00100	Р	\checkmark					

316L H20

Drossuro Pango	Droscuro Bongo Codo	H20 Unit	Process Connection Code			
Pressure Range	Pressure Range Code		L			
0 - 24	00024	Н	\checkmark			
0 - 48	00048	н	\checkmark			
0 - 69	00069	н	\checkmark			
0 - 100	00100	н	\checkmark			
0 - 120	00120	н	\checkmark			
0 - 208	00208	Н	\checkmark			
0 - 240	00240	н	\checkmark			
0 - 360	00360	н	\checkmark			
0 - 600	00600	Н	\checkmark			
0 - 1380	01380	Н	\checkmark			
0 - 2770	02770	Н	\checkmark			

 $^{\ast}\mbox{See}$ Ordering Information for list of options.

Ordering Information

AST45PT		1	L	00005	Р	4	Х	1	Ν	065
Temperature Outpu 1= -40 to 85°C (-40 to 185° 2= -40 to 125°C (-40 to 250 3= 0 to 70°C (30 to 158°F) 4= -55 to 125°C (-65 to 250 5= -18 to 93°C (0-200°F)	F) I°F)									
Process Connectio										
Pressure Range Insert Pressure Range Cod	le (see table for availability)									
Pressure Unit H= Inches H ₂ O P= PSI										
Output 3= 1-5V 4= 4-20mA										
Electrical Connecti N= Conduit fitting, Cable 6 P= Conduit fitting, Cable 10 X= Optional Length (see op	ft.) ft.									
Wetted Material 1= 316L / 304 / Hytrel (cabl	le) / Kynar (cord grip)									
Fail Condition N= Not Specified H= Fail High L= Fail Low										
Option Codes 140= 15 ft. (4.6 m) 075= 20 ft. (6.1 m)	074= 25 ft. (7.6 m) 004= 35 ft. (10.7 m)	130= 40 ft. 065= 50 ft.		003= 100 ft. 050= 150 ft.						

NORTH AMERICA

American Sensor Technologies, Inc. (AST), a TE Connectivity Company Tel: 800-522-6752 Email: <u>customercare.molive@te.com</u> ASIA

Hong Kong Sensor Technologies (HKST), a TE Connectivity Company Tel: 0400-820-6015 Email: <u>customercare.shzn@te.com</u>

TE.com/sensors

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.