



## DSE 1610.15 AHZ & DSE 1810.35 SHZ

### Variable Reluctance Speed Sensor

#### Product ID

Type #	Product #	Drawing #
DSE 1610.15 AHZ	3042607017	117617
DSE 1810.35 SHZ	3042608902	120816

#### General

**Function** the DSE 1610.15 AHZ and DSE 1810.35 SHZ series variable reluctance (VR) speed sensors consist of an iron core, an inductive coil, and a permanent magnet. A ferrous pole wheel passing the sensor face changes the magnetic field strength, resulting in an AC voltage being induced in the coil. The frequency of the output signal is proportional to the speed of the moving target. The amplitude of the signal depends on speed, air gap, geometry of target, magnetic properties of target material, and the electrical load. VR sensors, also known as passive or electromagnetic sensors, do not require an external supply.

#### Technical data

<b>Coil properties</b>	<ul style="list-style-type: none"> <li>● Inductance @ 1 kHz: 50 mH ± 10%</li> <li>◆ Resistance: 230 Ohm ± 10%</li> <li>◆ Magnet polarity: north pole towards front face</li> <li>◆ Pole piece: diameter 3 mm</li> </ul>
<b>Polarity</b>	According to drawing.
<b>Signal output</b>	<p>Using a sensor together with a toothed wheel having an involute gear form will generate a sinusoidal signal. Analysing the frequency will determine the rotational speed. The signal amplitude is proportional to the rate of change of magnetic flux generated by the pole wheel. In principle, it depends on the following parameters:</p> <ul style="list-style-type: none"> <li>◆ Circumferential velocity of the toothed wheel</li> <li>◆ Module of the toothed wheel</li> <li>◆ Air gap between toothed wheel and sensor's front surface</li> <li>◆ Load impedance applied to the sensor (recommended is 10 kOhm)</li> </ul> <p>Minimal voltage for 5 m/s circumferential speed, module 2 gear, 1 mm air gap and 10 kOhm load resistance: 3.6 Vpp</p>

## DSE 1610.15 AHZ & DSE 1810.35 SHZ

Variable Reluctance Speed Sensor

Frequency range	Up to 30 kHz, lower limit depending on application						
Housing	M16x1.5, tightening torque: max. 35 Nm						
Connection	<table border="1"><thead><tr><th>Type #</th><th>Connection [Jaquet part number]</th></tr></thead><tbody><tr><td>DSE 1610.15 AHZ</td><td>385E-73612 (connector)</td></tr><tr><td>DSE 1810.35 SHZ</td><td>824L-35053 (cable)</td></tr></tbody></table>	Type #	Connection [Jaquet part number]	DSE 1610.15 AHZ	385E-73612 (connector)	DSE 1810.35 SHZ	824L-35053 (cable)
Type #	Connection [Jaquet part number]						
DSE 1610.15 AHZ	385E-73612 (connector)						
DSE 1810.35 SHZ	824L-35053 (cable)						
Cable	<table border="1"><thead><tr><th>Jaquet cable type</th><th>Properties</th></tr></thead><tbody><tr><td>824L-35053</td><td>FEP cable, 4-wire (brown wire is not connected), 0.2 mm<sup>2</sup> (AWG 24), outer-Ø max. 4.2 mm, bending radius min. 60 mm, screened (metal net), white Operating temperature: -100°C to +150 °C</td></tr></tbody></table>	Jaquet cable type	Properties	824L-35053	FEP cable, 4-wire (brown wire is not connected), 0.2 mm <sup>2</sup> (AWG 24), outer-Ø max. 4.2 mm, bending radius min. 60 mm, screened (metal net), white Operating temperature: -100°C to +150 °C		
Jaquet cable type	Properties						
824L-35053	FEP cable, 4-wire (brown wire is not connected), 0.2 mm <sup>2</sup> (AWG 24), outer-Ø max. 4.2 mm, bending radius min. 60 mm, screened (metal net), white Operating temperature: -100°C to +150 °C						
connector	<table border="1"><thead><tr><th>Jaquet connector type</th><th>Manufacturer code</th></tr></thead><tbody><tr><td>385E-73612</td><td>Connector mates with straight plug MS3106A-10SL-4S, 2 pins</td></tr></tbody></table>	Jaquet connector type	Manufacturer code	385E-73612	Connector mates with straight plug MS3106A-10SL-4S, 2 pins		
Jaquet connector type	Manufacturer code						
385E-73612	Connector mates with straight plug MS3106A-10SL-4S, 2 pins						
Requirements for Pole wheel	Toothed wheel of a ferrous material (e.g. Steel 1.0036). Optimal performance with <ul style="list-style-type: none"><li>◆ Involute gear</li><li>◆ Tooth width &gt; 10mm</li><li>◆ Side offset &lt; 0.2 mm</li><li>◆ Eccentricity &lt; 0.2 mm</li></ul>						
Air gap between sensor and pole wheel	Depending on lowest circumferential speed which has to be detected and on trigger level.						
insulation	Housing and electronics galvanically separated (500 V/50 Hz/ 1 min)						
Temperature	Operating temperature of entire sensor: -40°... +125°C						

### Further Information

Safety	All mechanical installations must be carried out by an expert. General safety requirements have to be met.
Connection	The sensors must be connected according to sensor drawing. Sensor wires are susceptible to radiated noise. Therefore, the following points have to be considered when connecting a sensor: The sensor wires must be laid as far as possible from large electrical machines. They must not run parallel in the vicinity of power cables. It is advantageous to keep the distance between sensor and instrument as short as possible. If the signal requirements are met, the sensor cable may be lengthened via a terminal box located in an IP20 connection area in accordance with EN 60529.
Installation	The sensor has to be aligned to the pole wheel according to the sensor drawing. Deviations in positioning may affect the performance and decrease the noise immunity of the sensor. During installation, the smallest possible pole wheel to sensor gap should be set. The amplitude of sensor's output signal depends on decreases with increasing air gap. Hence, the gap should however be set to prevent the face of the sensor ever touching the pole wheel. A sensor should be mounted with the middle of the face side over the middle of the pole wheel. Dependent upon the wheel width, a certain degree of axial movement is permissible. However, the middle of the sensor must be at minimum in a distance of 3 mm from the edge of the pole wheel under all operating conditions. A solid and vibration free mounting of the sensor is important. Eventual sensor vibration relative to the pole wheel can induce additional output pulses. The sensors are insensitive to oil, grease etc. and can be installed in arduous conditions.

## DSE 1610.15 AHZ & DSE 1810.35 SHZ

Variable Reluctance Speed Sensor

Maintenance	Product cannot be repaired.
Transport	Product must be handled with care to prevent damage of the front face.
Storage	Product must be stored in dry conditions. The storage temperature corresponds to the operation temperature.
Disposal	Product must be disposed of properly, it must not be disposed as domestic waste.

### CONTACT US

Tel +41 61 306 8822

[jaquet.info@te.com](mailto:jaquet.info@te.com)

### te.com/sensorsolutions

JAUQUET, TE Connectivity, and TE connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2017 TE Connectivity Ltd. family of companies All Rights Reserved.