

940 Receptacle angled rotatable

speedtec - ready 6-pin Earth-to-Housing Connection according to VDE 0627 flange mount /Flange 40x40 Anti-vibration o-ring

C ED E 270 NN 00 00 0051 000 C G E 270 N 00 00 0051 000



Contact Arrangement mating view



zinc diecast / collinox PA 6.6 mod., UL 94/V0

Contacts (not part of product contents)


Tools (not part of product contents)

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz





Main Dimensions Receptacle angled rotatable

*for max. wire cross-section pay attention to the cross-section of used contacts

temperature range protection type rotation range **Electrical Data** rated current

Technical Data

number of pins

power signal

power max. 75 A* 630V (AC/DC) rated insulation voltage (L-L) 6000 V

max. 30 A* 250 V (AC/DC) 4000 V

when connected IP 66/67 330°



Material

housing insulation insert seals

pollution degree over voltage category

max. height for operation

rated voltage

500

6

2

4 (3+PE)

-20 °C to 130 °C

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

signal

III 2000 m

FKM