



JOINTING SYSTEM MXSU

FOR 1-CORE POLYMERIC CABLES UP TO 36(42) kV WITH MECHANICAL CONNECTORS

KEY FEATURES

- All inclusive kit
- Based on elastomeric triple layers joint sleeve
- Short and slim design
- Requires no crimping tool
- Includes mechanical connectors
- Meets CENELEC HD 629

TE Connectivity's (TE) Raychem MXSU jointing system offer a comprehensive range of joints for all cable types. TE's Raychem MXSU are based on a joint design using mechanical connectors for conductor and wire shields which are also supplied with the kit.

The kits are widely range taking and cover most conductor constructions including their tolerances. Due to the mechanical connectors the joints are easy to install with no crimping tools needed when connecting the cables and no tool maintenance required.

TE's Raychem MXSU are short joints of a space saving design, an essential characteristic when space is limited.

Reliability and performance are essential when it comes to customer demands and the MXSU exceeds international performance standards including CENELEC HD 629 or IEC 60502-4 for joints.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.

Jointing System MXSU

Meets international performance standards including CENELEC HD 629 or IEC 60502-4 for joints.



PRODUCT SELECTION INFORMATION: DIMENSIONS IN MM

Description	Cross Section Range [mm²]				Diameter Conductor	Diameter Over Core Insulation	Diameter Cable Over Sheath
	12 kV	17.5 kV	24 kV	36 kV			
MXSU-3111	25 - 95	-	-	-	5.2 - 12.0	13.2 - 21.8	23 - 32
MXSU-3121	70 - 150	-	-	-	8.7 - 15.0	17.6 - 24.3	25 - 38
MXSU-3131	95 - 240	-	-	-	10.3 - 19.2	18.6 - 29.4	26 - 41
MXSU-3132	150 - 300	-	-	-	12.9 - 21.6	21.6 - 31.4	29 - 43
MXSU-3141	240 - 400	-	-	-	17.8 - 24.6	25.0 - 34.6	33 - 47
MXSU-3151	500	-	-	-	25.5 - 27.6	33.8 - 37.2	44 - 50
MXSU-3161	630	-	-	-	27.9 - 32.5	39.9 - 40.0	47 - 54
MXSU-3171	800	-	-	-	32.5 - 35.3	38.5 - 42.6	52 - 57
MXSU-3181	1000	-	-	-	38.5 - 39.2	45.0 - 47.6	59 - 64
MXSU-4111	-	50 - 95	-	-	7.2 - 12.0	17.6 - 24.0	24 - 38
MXSU-4121	-	70 - 150	-	-	8.7 - 15.0	19.9 - 27.5	28 - 39
MXSU-4131	-	120 - 240	-	-	11.0 - 19.2	22.0 - 31.6	28 - 44
MXSU-4132	-	150 - 300	-	-	12.9 - 21.6	23.5 - 32.6	31 - 45
MXSU-4141	-	240 - 400	-	-	17.8 - 24.6	28.4 - 36.8	35 - 50
MXSU-4151	-	500	-	-	25.5 - 27.6	36.2 - 39.6	48 - 56
MXSU-5111	-	-	25 - 95	-	5.2 - 12.0	17.9 - 26.0	24 - 38
MXSU-5121	-	-	50 - 150	-	7.2 - 15.0	19.5 - 29.5	27 - 41
MXSU-5131	-	-	95 - 240	-	10.3 - 19.2	22.5 - 33.6	31 - 44
MXSU-5132	-	-	150 - 300	-	12.9 - 21.6	25.0 - 34.6	32 - 46
MXSU-5141	-	-	240 - 400	-	17.8 - 24.6	29.4 - 38.8	38 - 50
MXSU-5151	-	-	500	-	25.5 - 27.6	37.2 - 41.6	48 - 54
MXSU-5161	-	630	630	-	27.9 - 32.5	39.2 - 44.7	50 - 58
MXSU-5171	-	-	800	-	32.5 - 35.3	44.2 - 46.9	58 - 61
MXSU-5181	-	-	1000	-	38.5 - 39.2	49.4 - 53.2	64 - 67
MXSU-6111	-	-	-	35 - 95	6.0 - 12.0	24.0 - 30.0	32 - 43
MXSU-6121	-	-	-	70 - 150	8.7 - 15.0	26.2 - 34.5	34 - 44
MXSU-6131	-	-	-	150 - 300	13.9 - 21.6	31.1 - 39.6	38 - 53
MXSU-6141	-	-	-	240 - 400	17.8 - 24.6	36.2 - 42.8	40 - 54
MXSU-6151	-	-	-	500	25.5 - 29.2	40.1 - 46.6	44 - 60
MXSU-6161	-	-	-	630	29.0 - 32.5	45.8 - 50.5	55 - 68
MXSU-6171	-	-	-	800	32.5 - 35.3	50.1 - 53.4	62 - 66
MXSU-6181	-	-	-	1000	38.5 - 39.2	55.7 - 58.8	69 - 73

FOR MORE INFORMATION: TE Technical Support Centers

USA: +1 800 327 6996
 Canada: +1 (905) 475-6222
 Mexico: +52 (0) 55-1106-0800
 Latin/S. America: +54 (0) 11-4733-2200
 France: +33 380 583 200
 UK: +44 0870 870 7500
 Germany: +49 896 089 903
 Spain: +34 916 630 400
 Italy: +39 333 250 0915
 Benelux: +32 16 508 695
 Russia: +7 495-790 790 2-200
 China: +86 (0) 400-820-6015

te.com/energy

©2018 TE Connectivity. All Rights Reserved. EPP-2241-10/18-EN

Raychem, TE Connectivity and TE Connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.