

GUROSIL GEL FILLED JUNCTION BOX

INCLUDING TERMINAL STRIP, EASY TO CAST, RELIABLE SEAL

KEY FEATURES

- IP68 proven casting
- Good electrical insulation
- Self-repairing and self-resealing
- Easy to remove

TE Connectivity's (TE) GUROSIL Gel filled OBO Junction Box T40 is designed to protect electrical connections from the ingress of water used in rooms with high humidity effects as well as in outdoor applications. It also provides reliable protection against humidity, mechanical shock, and vibration.

GUROSIL Gel is a soft-elastic hardening, amber cold casting compound that is based on hydrocarbon resins. Quick and clean casting is simple with the help of customary caulking guns, so no special tools are required.

It is easy to remove, repairable and self-resealing. Electrical connections can be tested and repaired quickly where required, even after installation had been finished. It is also halogen-, silicon-, and isocyanate- free.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.



Gurosil Gel Filled Junction Box







TE's GUROSIL Gel is environmentally friendly, and not subject to any labelling requirements.

TECHNICAL DATA		
Application	Rooms with high humidty effect or outdoors	
Protection class	IP68, tested up to 18 m water depth for over 1000 h	
Nominal voltage	400 V	
Dielectric Strength	> 20 kV/mm	
Cable Diameter	6 x 1 mm ² , 5 x 1,5 mm ² or 4 x 2,5 mm ² per connection	
Cable Entry	7 x M25 including plug-in seals for cable diameter 4 - 20 mm	
Terminal System	Terminal block 4 mm², 5-poles, pluggable	
Enclosure Material	Shock-resistant and flame retardant plastic material	
Enclosure Colour	Light grey (RAL 7035)	
Dimension L x W x H	90 x 90 x 52 mm	

ORDERING INFORMATION			
Description	Description	Part Number	
GUROSIL-GEL-SETIP68	Junction Box, Terminal Strip and Gurosil Gel Cartridge incl. Mixer	CP6931-000	
GUROSIL-GEL(REFILL)	Gurosil Gel Cartridge incl. Mixer	CP6932-000	

te.com/energy

©2014 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-2251-10/14

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Technical Support Centers

USA: + 1 800 327 6996 + 33 380 583 200 + 44 0870 870 7500 France: UK: + 49 896 089 903 Germany: Spain: + 34 916 630 400 Benelux: + 32 16 351 731 Canada: +1 (905) 475-6222 + 52 (0) 55-1106-0800 + 54 (0) 11-4733-2200 Mexico: Latin/S. America: + 86 (0) 400-820-6015 China:

