

COLD APPLIED ELBOW SEAL (CES)

600 AMP CLASS FOR 1/C JACKETED CABLES (15 KV - 35 KV)

KEY FEATURES

- **Highly elastic EPDM formulation enables wide cable application ranges. Just three products are able to cover the most common range of cable, 15 kV #2 - 35 kV 1250 kcmil**
- **No open flame or heat source is required for installation**
- **Meets IEEE 404 jacket sealing requirements**
- **Thick walled tube resists puncture and damage**
- **Resistant to fungus, acids, and alkalis**

TE Connectivity's (TE's) CES Cold Applied Elbow Sealing Kit is used for sealing power cables where elbows or other cable accessories are installed. The CES is applied in 15 - 35 kV, 600A applications. It protects underground cable from moisture and airborne contaminants, and is suitable for both direct burial and submersible applications.

The kit consists of a factory-expanded tubular EPDM rubber sleeve on a spiral holdout, along with strips of mastic which are used to help create the seal.

Designed for easy field installation. After applying the mastic and cable accessory, the spiral holdout is simply pulled clear. The jacket will compress and, in combination with the mastic, form an environmental seal. An ergonomically designed spiral holdout provides a smooth installation with low release forces

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.

Cold Applied Elbow Seal CES




Figure A
Typical Installation of ELB-600-CES

PRODUCT DIMENSIONS

Description	Typical Expanded Tube Length	Typical Relaxed Tube Length	Inner Diameter of Holdout
ELB-600-CES-1	5.00 (127)	6.00 (150)	1.97 (50)
ELB-600-CES-2	6.75 (171)	8.00 (200)	2.68 (68)
ELB-600-CES-3	7.50 (190)	9.00 (225)	3.85 (98)

PRODUCT SELECTION INFORMATION

Description	Cable Size 15 kV Class	Cable Size 25 kV Class	Cable Size 35 kV Class	Min. Seal Diameter	Max. Installed Diameter
ELB-600-CES-1	2 - 4/0 AWG (35 - 100 mm ²)	2 - 2/0 AWG (35 - 50 mm ²)	1/0 AWG (60 mm ²)	0.95" (24 mm)	1.5" (38 mm)
ELB-600-CES-2	2/0 - 1000 kcmil (70 - 500 mm ²)	1/0 AWG - 750 kcmil (60 - 380 mm ²)	1/0 AWG - 500 kcmil (60 - 250 mm ²)	1.28" (33 mm)	2.67" (68 mm)
ELB-600-CES-3	750 - 1500 kcmil (380 - 725 mm ²)	600 - 1250 kcmil (325 - 625 mm ²)	350 - 1250 kcmil (180 - 625 mm ²)	1.60" (41 mm)	3.50" (89 mm)

KITS WITH EXTERNAL GROUNDING COMPONENTS

Catalog Number	Cable Size 15kV Class	Cable Size 25kV Class	Cable Size 35kV Class	Minimum Seal Dia.	Maximum Installed Dia.
ELB-600-CES-GRD-1	2 - 4/0 AWG (35 - 100mm)	2 - 2/0 AWG (35 - 50mm)	1/0 (60mm)	0.95" (24mm)	1.50" (38mm)
ELB-600-CES-GRD-2	2/0 - 1000 kcmil (70 - 500mm)	1/0 - 750 kcmil (60 - 380mm)	1/0 - 500 kcmil (60 - 250mm)	1.28" (33mm)	2.67" (68mm)
ELB-600-CES-GRD-3	750 - 1500 kcmil (380 - 725mm)	600 - 1250 kcmil (325 - 625mm)	350 - 1250 kcmil (180 - 625mm)	1.60" (41mm)	3.50" (89mm)

PRODUCT SELECTION INFORMATION

1. Selections are based on the typical dimensions of 100% insulated cables, manufactured in accordance with AEIC standard. Nominal insulation thickness (100%): 15 kV:175mils, 25 kV:260mils, 35 kV:345mils.
2. Select the appropriate catalog number. Use the actual insulation OD, and jacket OD range as the final ordering criteria.
3. For other applications or if you have any questions, contact your TE representative.
4. If ordered separate from Elbow kits, standard package: 3 kits per box.
5. Related test reports: EDR-5528

te.com/energy

© 2020 TE Connectivity. All Rights Reserved. EPP-2686-DDS-5/20-EN-AMS-CES-Raychem E404

TE Connectivity, TE connectivity (logo), EVERY CONNECTION COUNTS, AMP, AMPACT, Axicom, Bowthorpe EMP, Crompton Instruments, Raychem, SIMEL, UTILUX are trademarks. Other logos, product and Company names mentioned herein may be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Technical Support Centers

USA/Canada:	+1 800-327-6996
Brazil:	+55 11-2103-6023
Mexico:	+52 55-1106-0800
South America:	+57 1-319-8962
Benelux:	+32 16-508-695
France:	+33 (0) 38-058-3210
Germany/Switzerland:	+49 (0) 89-608-9903
Italy:	+39 335-834-3453
Middle East/Africa:	+971 4-211-7020
Russia:	+7 495-790-790-2-200
Spain/Portugal:	+34 912-681-885
UK:	+44 08708-707-500
China:	+86 400-820-6015