





# DO-35 GLASS AXIAL NTC THERMISTORS

Glass Encapsulation
Ø 1.9mm Diameter
Axial 24 AWG Tin/Nickel Plated Copper Leads
RoHS Compliant

The DO-35 Series NTC Thermistor is hermetically sealed in a DO-35 diode style glass encapsulated package. The rugged package can be used in applications with a temperature range of -40°C to +250°C. The leads are suitable for welding or soldering. The axial leads make this device suitable for PC board mounting.


### **FEATURES**

- 5K to 200K Ohms Resistance @ 25C
- Proven Stability and reliability
- Temperature range -40°C to +250°C

#### **APPLICATIONS**

- Consumer electronics
- PCB temperature sensing
- Air conditioning
- Low cost probe assemblies

# **MECHANICAL DETAILS**



# **STABILITY**

Reliability Tests	Standard	Test Condition	Delta R
Storage in Dry Heat	IEC 60068-2-2	Storage temperature: 200°C & 250°C Duration: 1000 hours	< 3%
Storage in Damp Heat	IEC 60068-2-3	Temperature of air is 40°C & RH 93% Duration: 56 days	< 2%
Rapid Temperature Cycling	IEC 60068-2-14	Lower Test Temperature -55°C Upper Test Temperature +200°C Number of Cycles 50	< 2%

## **ORDERING INFORMATION**

Part Number	Resistance [Ω] @ +25°C	Tolerance @ +25°C	Beta Value 25/85	Beta Tolerance	Operating Temperature
GA5KF3550DPGS	5,000	± 1%	3550	± 2%	-40° to +200°C
GA10KF3270DPGN	10,000	± 1%	3270	± 2%	-40° to +250°C
GA10KF3435DPGS	10,000	± 1%	3435	± 2%	-40º to +200ºC
GA10KF3550DPGN	10,000	± 1%	3550	± 2%	-40° to +250°C
GA10KF3700DPGN	10,000	± 1%	3700	± 2%	-40º to +250ºC
GA10KF3950DPGN	10,000	± 1%	3950	± 2%	-40º to +250ºC
GA10KF3960DPGN	10,000	± 1%	3960	± 2%	-40º to +250ºC
GA10KF3975DPGS	10,000	± 1%	3975	± 2%	-40º to +200ºC
GA20KF3960DPGN	20,000	± 1%	3960	± 2%	-40º to +250ºC
GA50KF3950DPGN	50,000	± 1%	3950	± 2%	-40º to +250ºC
GA50KF3960DPGN	50,000	± 1%	3960	± 2%	-40º to +250ºC
GA100KF3975DPGN	100,000	± 1%	3975	± 2%	-40º to +250ºC
GA100KF4300DPGN	100,000	± 1%	4300	± 2%	-40º to +250ºC
GA200KF4000DPGN	200,000	± 1%	4000	± 2%	-40º to +250ºC

**NORTH AMERICA** Tel +1 800 522 6752

rel +1 800 522 6752 customercare.ando@te.com EUROPE
Tel +31 73 624 6999
customercare.qlwv@te.com

ASIA

Tel +86 0400 820 6015 customercare.chdu@te.com

#### te.com/sensorsolutions

TE Connectivity, TE, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, products and/or company names referred to herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2018 TE Connectivity Ltd. family of companies All Rights Reserved.