



Eliminates management
of calibration data



11207AC Angular Rate Sensor

SPECIFICATIONS

- Rugged Uniaxial Angular Rate Gyro
- Low Noise Vibration Rejecting Rate Gyro
- $\pm 300^\circ/\text{sec}$ Dynamic Range
- Interchangeable Sensors, Identical Calibrations
- High Stability, Temperature Compensated
- 10 to 36Vdc Excitation Voltage

The TE Connectivity model 11207AC Angular Rate Sensor is a rugged uniaxial analog gyroscope capable of accurately measuring angular rate under severe environmental conditions. The Gyro Sensor design rejects linear acceleration and vibration influences, making the model 11207AC Angular Rate Gyro extremely stable, even in high shock and vibration environments.

The angular rate sensor is packaged in a tough, compact housing with fully encapsulated and protected electronics and a shielded 22 AWG cable. Its cubical form allows mounting with the sensing axis oriented in any direction.

Each angular rate sensor has been accurately tested and compensated over the full -40°C to $+85^\circ\text{C}$ temperature range and has a nominal full scale output swing of $\pm 2.25\text{V}$. The zero rate output level is nominally $+2.5\text{Volts}$.

FEATURES AND BENEFITS

Identical™ Interchangeable Sensor

Identical™ Interchangeable Sensors eliminate the management of calibration data and allow convenient Interchangeability of individual sensors. With standardized sensitivity and offset, there is no need to enter new parameters for each unit. Perfect for high volume use.

Rugged for Harsh Environment

The 11207AC is robust to perform well in harsh environments. The 6061-T6 case with electroless nickel finish plus a PTFE cable with a shield bonded to the case provide improved resistance to EMI, lightning, or other disturbances.

High Accuracy and Linearity over Wide Temperature Range

The output of the 11207AC sensor is directly proportional to the rotational rate about its axis. The DC-coupled output is fully scaled, referenced, and temperature compensated. When used in demanding temperature environments, gain compensation makes the 11207AC one of the most accurate angular rate gyros available.

PERFORMANCE SPECIFICATIONS

All values are typical at +24°C and 12Vdc excitation unless otherwise stated. TE Connectivity reserves the right to update and change these specifications without notice.

Parameters

DYNAMIC

Dash Number	-R300
Range (deg/sec)	±300
Sensitivity (mV/deg/sec)	7.5 ±1%
Frequency Response (Hz)	0-100
Non-Linearity (%FSO)	±0.01
Alignment (deg)	±1.5
Influence of Linear Acceleration (°/sec/g)	0.015
Shock Limit (g)	±10,000
Noise Density (°/sec/√Hz)	0.01

Notes

See Ordering Info
 Identical, see note 1 below
 Upper cutoff -3dB
 BFSL
 Deviation from ideal axes
 Affects offset
 0.5msec pulse

ELECTRICAL

Zero Acceleration Output (V)	2.50 ±0.10
Excitation Voltage (Vdc)	10 to 36
Excitation Current (mA)	10
Rejection Ratio (dB)	>120
Full Scale Output Voltage (Vpk)	0.25 to 4.75
Insulation Resistance (MΩ)	>100
Output Impedance (Ω)	100
Turn On Time (msec)	<100
Ground Isolation	Isolated from Mounting Surface

No load, quiescent
 DC
 Iout = 1mA, cap load <1000pF
 @100Vdc

ENVIRONMENTAL

Thermal Zero Shift (°/sec)	±1.0 typical (±6.0 max)
Thermal Sensitivity Shift (%)	±1.0
Operating Temperature (°C)	-40 to +85
Humidity (Active Element & Electronics)	Hermetically Solder Seal
Humidity (Housing)	Epoxy Sealed, IP65

-40 to +85°C
 -40 to +85°C

PHYSICAL

Case Material	Electroless Nickel Plated 6061-T6 Aluminum
Cable	4x, #22 AWG Conductors, PTFE Insulated, Tin Plated Shield, PTFE Jacket
Weight (cable not included)	38 grams
Mounting	2x M3-0.5 Machine Screws
Mounting Torque	5 lbf-in (0.56 N-m)

Note 1 Identical are interchangeable, all units have same range and sensitivity




Calibration supplied:	CS-ARLIN	NIST Traceable Calibration with Sensitivity and Offset
Optional accessories:	34170B	Adaptor Plate for Flange Mounting


The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. TE Connectivity reserves the right to make changes without further notice to any product herein. TE Connectivity makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does TE Connectivity assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. TE Connectivity does not convey any license under its patent rights nor the rights of others.

11207AC ANGULAR RATE SENSOR


DIMENSIONS



SCHEMATIC



Option D: DB9 Male Connector



- Pin 1: +OUTPUT SIGNAL
- Pin 2: -OUTPUT SIGNAL
- Pin 3: NOT USED
- Pin 4: NOT USED
- Pin 5: NOT USED
- Pin 6: NOT USED
- Pin 7: NOT USED
- Pin 8: +EXCITATION VOLTAGE
- Pin 9: -EXCITATION VOLTAGE (GND)

ORDERING INFORMATION

11207AC RXXX BYYY TZZZA

Range

R300 = ± 300 deg/sec

Bandwidth

B100 = 0 to 100Hz (standard option)

BYYY = Contact factory for wider bandwidth option

Cable Length

T004 = 4ft cable (standard option)

TZZZ = Contact factory for custom length (ZZZ in feet)

Cable Termination

A = None, flying leads

D = 9-pin DB9 male connector

Example; 11207AC-R300-B100-T004A

Model 11207AC, ± 300 deg/sec range, 0-100Hz bandwidth, 4ft cable length, flying leads

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Phone +1-800-522-6752
Email: customercare.akrn@te.com

EUROPE

MEAS France SAS
a TE Connectivity Company
Phone: +49-800-440-5100
Email: customercare.tlse@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Phone: +86-400-820-6015
Email: customercare.shzn@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Accustar, American Sensor Technologies, AST, ATEXIS, DEUTSCH, IdentiCal, TruBlue, KPSI, Krystal Bond, Microfused, UltraStable, Measurement Specialties, MEAS, Schaevitz, TE Connectivity, TE, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and company names mentioned herein may be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.