



DSD 1005.00 xTV AND FTG 1088.xx

HALL EFFECT SINGLE CHANNEL SPEED SENSOR

Product ID

Type #	Product #	Drawing #
DSD 1005.00 KTV (old type: FTG 1088.00)	343Z-03828	4-106.026B
DSD 1005.00 PTV (old type: FTG 1088.01)	343Z-03835	4-106.026B

General

Function The sensors DSD 1005.00 xTV (FTG 1088.xx) are suitable, in conjunction with a pole wheel, for generating square wave signals proportional to rotary speeds. The sensing element consists of a magnetically biased differential hall effect semiconductor in a bridge-circuit, followed by a Schmitt-trigger. The latter has an open collector output connected to the positive pole of the power supply through a 1.8k resistor.
The DSD 1005.00 xTV (FTG 1088.xx) have a dynamic behavior, so that pulse generation is guaranteed down to a speed corresponding to a frequency of 5 Hz.

Technical data

Supply voltage	4.5 -24 VDC
Current consumption	Max. 16 mA (without load)

DSD 1005.00 xTV AND FTG 1088.xx

HALL EFFECT SINGLE CHANNEL SPEED SENSOR

Signal output	<ul style="list-style-type: none">• Square wave signal<ul style="list-style-type: none">• Signal levels without load UHigh ~ Upower supply, ULow < 0.4 V• Max. allowed sink current = 25mA (at a saturation voltage < 0.4V)• The output is connected through a pull-up resistor of 1.8 kOhm to the positive pole of the power supply
Frequency range	DSD 1005.00 xTV (FTG 1088.xx): 5Hz...20 kHz
Electromagnetic compatibility (EMC):	According to 89/336/EWG, EN 50081-2, EN 50082-2: <ul style="list-style-type: none">• Electrostatic discharge into housing, cable shield and wires: up to ±4 kV peak according to IEC 61000-4-2, severity level 2• Radiated electromagnetic field: up to 30 V/m, 50% AM, 1 kHz in the range of 1 MHz to 1000 MHz according to IEC 61000-4-3, severity level 3• Electrical fast transients/bursts, coupled to sensor cable with a capacitive coupling clamp: up to ±4 kV peak according to IEC 61000-4-4, severity level 4
Housing	Argentan (German silver) CuNi10Zn42Pb DIN 2.0770, front side sealed hermetically, sensor components potted in chemical and age proof synthetic resin. Dimensions per drawing.
Pole wheel	Toothed wheel made of a magnetically permeable material (e.g. Steel 1.0036) <ul style="list-style-type: none">• Minimum tooth width 10 mm• Side offset < 0.2 mm• Eccentricity < 0.2mm• Involute gear wheel preferred (module ≥0.5)
Air gap sensor / pole wheel	Air gap between pole wheel (involute gear) and sensor housing: DSD 1005.00 xTV (FTG 1088.xx): <ul style="list-style-type: none">• Module 0.5 mm: 0.1...0.4 mm• Module 1.0 mm: 0.1...1.0 mm• Module 2.0 mm (and larger): 0.1...1.3 mm
Insulation	Housing and electronics galvanically separated (500 V/50 Hz/ 1 min)
Protection class	IP68 (head) and IP67 (cable or litz wire outlet)
Vibration immunity	3 g in the range 4...100 Hz
Shock immunity	20 g during 11 ms, half-sine wave.
Operating temperature	-40°C...+125°C

Further Information

Safety	All mechanical installations must be carried out by an expert. General safety requirements have to be met.
Connection	The sensors must be connected according to sensor drawing. Sensor wires are susceptible to radiated noise. Therefore, the following points have to be considered when connecting a sensor: The sensor wires must be laid as far as possible from large electrical machines. They must not run parallel in the vicinity of power cables. The maximum permissible cable length is dependent upon the sensor voltage, the cable routing, along with cable capacitance and inductance. However, it is advantageous to keep the distance between sensor and instrument as short as possible. The sensor cable may be lengthened via a terminal box located in an IP20 connection area in accordance with EN 60529.
Installation	The sensor has to be aligned to the pole wheel according to the sensor drawing independent of its rotational orientation. Deviations in positioning may affect the performance and decrease the noise immunity of the sensor. During installation, the smallest possible pole wheel to sensor gap should be set. The gap should however, be set to prevent the face of the sensor ever touching the pole wheel. The amplitude of the output signal is not influenced by the air gap. A sensor should be mounted with the middle of the face side over the middle of the pole wheel. Dependent upon the wheel width, a certain degree of axial movement is permissible. However, the middle of the sensor must be at minimum in a distance of 3 mm from the edge of the pole wheel under all operating conditions. A solid and vibration free mounting of the sensor is important. Eventual sensor vibration relative to the pole wheel can induce additional output pulses. The sensors are insensitive to oil, grease etc. and can be installed in arduous conditions. Within the air gap specified the amplitude of the output signals is not influenced by the air gap.
Maintenance	Product cannot be repaired
Transport	Product must be handled with care to prevent damage of the front face.
Storage	Product must be stored in dry conditions. The storage temperature corresponds to the operation temperature.
Disposal	Product must be disposed of properly; it must not be disposed as domestic waste.

CONTACT US

Tel +41 61 306 8822
jaquet.info@te.com

te.com/sensor solutions

JAQUET, TE Connectivity, and TE connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2017 TE Connectivity Ltd. family of companies All Rights Reserved.