

FEATURES

- Static and dynamic applications
- Linearity 0.1% F.S.
- Integrated Amplifier optional
- IP65 optional

APPLICATIONS

- Process control equipment
- Weighing calibration tool
- Fatigue tests benches
- Hydraulic press regulation
- Laboratory and Research

FN3000

Load Cell Tension and Compression

SPECIFICATIONS

- Heavy duty Pan-cake load cell
- Standard ranges 10 kN to 1000 kN [2 klbf to 200 klbf]
- Very high stability
- Aluminum or Stainless steel body
- High IP protection available
- High Level Output Model with Integrated Amplifier

The **FN3000** measures tension and compression in standard ranges from 0-10 kN to 0-1000 kN. The mechanical design and gauge placement minimizes transverse effects. Depending on the range, the **FN3000** is constructed in aluminium alloy or stainless steel and is available with numerous options. It is suitable for test bench applications and used in many hostile environments and can be customized for increased protection.

With a long standing experience as a designer and manufacturer of sensors, TE CONNECTIVITY often works with customers to design or customize sensors for specific uses and testing environments.

To meet your needs we also offer extensive turnkey systems. The matched components (sensor, power, amplifier and digital display) are formatted, calibrated and ready for immediate use.

On request, Instruction documents can be provided to ease the selection and use of our sensors and provide helpful tips.

STANDARD RANGES

Ranges (FS) (N)	10k	25k	50k	100k	200k	500k	1000k
Ranges (lbf)	2.2k	5.6k	11.2k	22.5k	45.0k	112.4k	224.8k
Material	Aluminium	Stainless Steel					
Stiffness (N/m)	4.2E+08	1.1E+09	1.4E+09	2.6E+09	3.6E+09	5.9E+09	8.9E+09
Stiffness (lbf/ft)	2.9E+07	7.5E+07	9.6E+07	1.8E+08	2.5E+08	4.1E+08	6.1E+08

PERFORMANCE SPECIFICATIONS (typical values at temperature 23°C)

Version	Standard	A1	A2
Power supply	10Vdc	10Vdc à 30Vdc	±12Vdc à ±18Vdc
Sensitivity (FSO)	±20mV	±2Vdc ±0.2V	±5Vdc ±0.25V
Offset	<±1mV	2.5Vdc ±0.2V	0V ±0.25V
Input Impedance / Consumption	700 ohms	< 30 mA	
Output Impédance	700 ohms	1000 ohms	
Overrange Without Damage	1.5 x FS		
Overrange Without destruction	3 x FS		
Linearity	< ±0.1% FS		
Hysteresis	< ±0.1% FS		
Operating Temperature Range (OTR)	-20°C to +80°C		
Compensated Temperature Range (CTR)	0°C to +60°C		
Thermal Zero Shift in CTR	< 0.5% FS/50°C		
Thermal Sensitivity Shift in CTR	< 1%/50°C		
Insulation	> 1000 Mohms		
Protection index	IP50		

Notes

1. Signal goes positive in tension with standard wiring configuration. Other signal output on request
2. Electrical Termination: Connector output including mate
3. Materials: Body in stainless steel or aluminium alloy depending on F.S.; aluminum cover
4. Protection Index: IP50 (other protection levels on request)
5. Output impedance < 100Ω on request
6. CE conformance according to EN 61010-1, EN 50081-1, EN 50082-1

DIMENSIONS & WIRING SCHEMATIC (IN METRIC AND IMPERIAL)

Wiring Schematic

Version -A1

Version -A2

OPTEHxxx: Hemispherical Load Button

Dimensions in mm

F.S.	J	R	ØD
10 KN	12	80	34
25 KN	12	80	34
50 KN	12	80	34
100 KN	20	250	65
200 KN	20	250	65
500 KN	30	400	87
1000 KN	60	400	120

OPTFFxxx: Tension pull plate

Dimensions in mm [inch]

Ranges in N	10k	25k	50k	100k	200k	500k	1000k
A	100 [3.94]			150 [5.91]	195 [7.68]	272 [10.71]	
B	30 [1.18]			40 [1.57]	60 [2.36]	80 [3.15]	
C	34 [1.34]			65 [2.56]	87 [3.43]	120 [4.72]	
D (Thread)	M20x1.5			M32x2	M56x2	M80x3	
E	65 [2.56]			90 [3.54]	106 [4.17]	150 [5.91]	
F	70 [2.76]			100 [3.94]	143 [5.63]	186 [7.32]	
G	45°			30°	22.5°		
H	8x8.2 /Φ85			12x10.4 /Φ125	16x16.2 /Φ169	16x24.5 /Φ229	
I	M8 /Φ85			M10 /Φ125	M16 /Φ169	M24 /Φ229	
Screw-down (m.kg)	2.2	2.5	2.5	5	5	15	50
Screw-down in lbf/ft	15.9	18.1	18.1	36.2	36.2	108.5	361.7

FN3000


Load Cell Tension and Compression

OPTIONS

Z04	CTR -40°C to +90°C (OTR -40°C to +90°C)
Z35	CTR +20°C to +120°C (OTR -20°C to +120°C)
Z36	CTR +20 to +150°C (OTR -20°C to +150°C) - Not available with A1/A2 versions

Other options may be offered as custom designed sensors. Please contact your local Customer Service.+

ORDERING INFO



SUPPLIED ACCESSORIES

EFMX-7M : mating plug Jaeger 530-272-006 with clamp 530-371-006 for standard and Z04 option
EFMX-7H : mating plug Jaeger 530-604-006 with clamp 530-693-006 for Z35 or Z36 options

RECOMMENDED ACCESSORIES

OPTEHxxx	10kN to 1000kN	Hemispherical load button (Contact us)
OPTFFxxx	10kN to 1000kN	Tension pull plate (Contact us)

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
Phone: +1 800 522 6752
Email: customercare.fmt@te.com

EUROPE

Measurement Specialties (Europe), Ltd.
a TE Connectivity Company
Phone: +31 73 624 6999
Email: customercare.lcsb@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
Phone +86 400 820 6015
Email: customercare.shzn@te.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.