

Energy Division


GMRS

Gray Mastic Rejacketing Sleeve

GMRS rejacketing sleeves quickly and conveniently seal and protect medium voltage cable splices up to 35 kV. GMRS rejacketing sleeves can also be used to repair cables with jacket damage. The robust, yet compact design is engineered to handle the harsh environments of manhole, direct buried or weather exposed applications.

- GMRS provides a watertight seal cover that can be used over all types and brands of push-on and cold-applied splices.
- GMRS design reduces installation space because it is not required to position a tube to the side while installing the splice. The result is easier installation in cramped man-holes and less digging for direct buried applications.

- Installation is literally a snap. Installers will appreciate the simple wrap-around design and dependable mastic sealing performance. To install, use the supplied pre-latch clips and installation snap tool – simply wrap and snap the sleeve on any cable in the use range.



Product Selection

Selection Information: dimensions in inches (millimeters)

Catalog Number	Sleeve Length	Cable Jacket O.D. Min.	Splice O.D. Max.	Maximum Jacket Opening
GMRS-75/25-650	25.5" (650)	1" (25)	2.5" (63)	17.5" (445)
GMRS-75/25-750	29.5" (750)	1" (25)	2.5" (63)	21.5" (545)
GMRS-75/25-850	33.5" (850)	1" (25)	2.5" (63)	25.5" (648)
GMRS-75/25-1050	41.25" (1050)	1" (25)	2.5" (63)	33.25" (820)
GMRS-75/25-1200	47.25" (1200)	1" (25)	2.5" (63)	39.25" (996)
GMRS-100/40-750	29.5" (750)	1.5" (38)	3.5" (89)	21.5" (545)
GMRS-100/40-850	33.5" (850)	1.5" (38)	3.5" (89)	25.5" (648)
GMRS-100/40-1050	41.25" (1050)	1.5" (38)	3.5" (89)	33.25" (820)
GMRS-100/40-1200	47.25" (1200)	1.5" (38)	3.5" (89)	39.25" (996)

Each kit includes a mastic strip (S1278) for external ground applications.

Ordering Information

1. Select the appropriate catalog number based on the cable diameter and the jacket opening. Cable and splice body must be within specified use range.
2. Standard package: 3 kits per box. Each kit contains one strip of mastic and one solvent wipe. Each box of 3 kits contains one installation snap tool and 2 pre-latch clips.
3. GMRS-75/25 and GMRS-100/40 meet the test requirements of IEEE 404-2006. Request EDR # 5507.

Installation of rejacketing sleeve using snap tool and pre-latch clips



Tyco Electronics Corporation
8000 Purfoy Road
Fuquay Varina, NC 27526-9349
Tel: 800.327.6996
Fax: 800.527.8350
E-mail: naenergy@tycoelectronics.com
<http://energy.tycoelectronics.com>
www.tycoelectronics.com
©2011 Tyco Electronics Corporation.
All rights reserved.
5-1773459-4 E400 01/11

All of the above information, including drawings, illustrations and graphic designs, reflects our present understanding and is to the best of our knowledge and belief correct and reliable. Users, however, should independently evaluate the suitability of each product for the desired application. Under no circumstances does this constitute an assurance of any particular quality or performance. Such an assurance is only provided in the context of our product specifications or explicit contractual arrangements. Our liability for these products is set forth in our standard terms and conditions of sale. GelWrapTE (logo) and Tyco Electronics are trademarks of the Tyco Electronics group of companies and its licensors. Other trademarks used are the property of their respective owners.

Energy Division – A pioneer in the development of economical solutions for the electrical power industry. Our product range includes: cable accessories, connectors & fittings, electrical equipment, instruments, lighting controls, insulators & insulation enhancement and surge arresters.