


COIL: @25°C

RESISTANCE $27\Omega \pm 10\%$
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 2.7 VDC
 MUST RELEASE .29 VDC

TOLERANCE UNLESS OTHERWISE SPECIFIED
 DECIMALS $\pm .005$ FRACTIONAL $\pm 1/64$



ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS AT 30 g's
 SHOCK 100 g's 6+1 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

CONTACT RATING: 2 AMP, 28 VDC
 Resistive Load 100,000
 Operations Minimum

NOTES:

DR. J. Brooks CK. 2-26-86



Communications
 Instruments, Inc.

CUST. CII
 CUST. NO N39016/6-132L

TYPE "HFW" RELAY

HFW 1130 L01