

### **HEAT SHRINK TUBING ZCSM**

# THICK-WALL LOW VOLTAGE FLAME-RETARDANT HALOGEN-FREE INSULATION AND OUTER SEALING TUBING

#### **KEY FEATURES**

- High electrical characteristics and mechanical strength for low voltage applications
- Thick-wall, cross-linked polyolefin. UV stabilised against irradiation and weathering
- Flame-retardant in accordance with IEC 60332-1. Approved for applications with safety class cables
- Halogen-free, non-corrosive, free of lead and aluminium
- Color black, 2.5:1 shrink ratio
- Unlimited shelf-life

TE Connectivity's (TE) Raychem ZCSM heat shrink thick-wall flame-retardant tubing is designed for insulation purposes on low voltage cable accessories and applications as well as providing mechanical protection on medium voltage accessories.

TE's Raychem ZCSM tubing is an uncoated, halogen-free, thick-wall type and low fire hazard tubing. It is used for jointing and protection of low fire hazard cables commonly used in offshore, marine, mining, shipbuilding, construction industry and transportation network and equipment.

The ZCSM tubing is approved for core insulating and as rejacketing of safety class cables, in high-rise buildings, public buildings, subways, road or railway tunnels requiring insulation or circuit integrity even under fire condition.

The optical smoke density produced by the ZCSM tubing in fire conditions has been measured in accordance with methods as defined in standard IEC 61034. The range of thick-wall ZCSM tubing provides protection to the same fire standards as modern low smoke, low fire hazard cable specifications.

The material content of the ZCSM tubing is halogen-free and stabilized against UV irradiation. The ZCSM tubing is fast and easily installed and has proven its long-term reliability in harsh climatic conditions and polluted environments. It also has an unlimited shelf-life when stored under normal conditions.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.



#### **Heat Shrink Tubing ZCSM**







Compliant to RoHS and REACH regulations. Approved for offshore applications.

TESTING					
Physical Characteristic	Test Method	Material Requirements			
Tensile Strength	ISO 37	8 MPa min.			
Ultimate Elongation	ISO 37	200 % min.			
Hardness	ISO 868	≥ 40 shore D			
Accelerated ageing 168 hrs at 150 °C ± 2 °C Tensile Strength Ultimate Elongation	ISO 188 ISO 37 ISO 37	8 MPa min 100% min			
Low Temperature Flexibility	ASTM D 2671	No cracking at 4 hours at -40 °C ± 3 °C			
Dielectric Strength	IEC 60243	10 kV/mm min.			
Volume Resistivity	IEC 60093	$1x10^{10} \Omega$ cm min.			
Water Absorption	ISO 62 proc. A	max. 0.3% after 24 h at 23 °C max. 0.7% after 14 days at 23 °C			
Flame-redardant Characteristics, Fire	Safety				
Flammability	IEC 60332-1 pass				
Flame propagation	IEC 60332-1	pass			
Limited oxygen index	ISO 4589	29 min.			
Temperature index	NES 715, type B	250°C min			
Smoke density	IEC 60134	on request			
Smoke index	NES 711	20 max.			
Acid gas generation	BR TDE 76-P-16	1,5% max.			
Toxicity index	NES 713 3 max.				
Corrosion	ASTM D 2671 Proc. A No corrosion after 16 h at 150 °C				
<b>Application Characteristics</b>					
Operating temperature range	- 40 °C up to + 120 °C				
Installation/shrinking temperature	> 125 °C				

PRODUCT SELECTION INFORMATION - DIMENSIONS IN MM							
Description	Application Range		Diameter		Wall Thickness		
	from	to	expanded min	recovered max	expanded nom	recovered min	
ZCSM 8/3	3.5	7	8	3	0.6	2.0	
ZCSM 16/5	5.5	14.5	16	5	0.7	2.4	
ZCSM 24/8	9	21.5	24	8	0.9	2.9	
ZCSM 32/12	13	29	32	12	1.0	4.0	
ZCSM 45/16	17.5	40.5	45	16	1.0	4.0	
ZCSM 60/22	24	54	60	22	1.0	4.0	
ZCSM 70/25	27.5	63	70	25	1.0	4.0	
ZCSM 85/36	39.5	76.5	85	36	1.0	4.0	
ZCSM 120/50	55	108	120	50	1.0	4.2	
ZCSM 180/75	82.5	162	180	75	1.0	4.2	

<sup>\*</sup> all sizes uncoated only

#### te.com/energy

© 2018 TE Connectivity. All Rights Reserved. EPP-0550-10/18-EN

Raychem, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and Company names mentioned herein may be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

## FOR MORE INFORMATION: TE Technical Support Centers

USA: + 1800 327 6996 + 1 (905) 475-6222 + 52 (0) 55-1106-0800 Canada: Mexico: Latin/S. America: + 54 (0) 11-4733-2200 France: + 33 380 583 200 + 44 0870 870 7500 UK: + 49 896 089 903 Germany: + 34 916 630 400 Spain: + 39 333 250 0915 Italy: Benelux: +32 16 508 695 Russia: +7 495-790 790 2-200 China: + 86 (0) 400-820-6015

