


COIL: @ +25 °C  
 RESISTANCE 700 OHMS ± 10%  
 NOMINAL VOLTAGE 26.5 VDC  
 MUST OPERATE 15.0 VDC  
 MUST RELEASE 8.0 VDC MAX 1.5 VDC MIN

ENVIRONMENT:  
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 100 g's 6 ± 1 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: MAXIMUM TRANSIENT SUPPRESSED VOLTAGE OF -48 VDC WITH BIFILAR COIL

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 2/8/93 CK2/8/93



CUST. OPL  
 CUST. NO. M39016/22-009L

TYPE "HMB" RELAY

HMB1201K01L