



RoHS

H(T)U(F)3500 SERIES

Analog Relative Humidity module with Temperature output

SPECIFICATIONS

- Compact plug and play module with no external component required
- Can operate under 5VDC or 3VDC
- Relative Humidity and Temperature Analog Output
- Full interchangeability. No calibration required
- Can operate under 5VDC or 3VDC
- Low power consumption
- Fast response time

Based on the new humidity sensor HTU21P, HTU3500 Series are dedicated humidity and temperature plug and play transducer designed for OEM applications where reliable and accurate measurements are needed. Direct interface with a micro-controller is made possible with the modules humidity linear voltage and direct NTC outputs. The HTU3500 Series are designed for high volume and demanding applications where power consumption is critical.

Optional PTFE filter/membrane (F) protects HTU3500 Series modules analog humidity modules with temperature output against dust, water immersion as well as against contamination by particles. PTFE filter/membrane preserves a high response time. Several connectors are proposed. 5VDC or 3VDC power supply products are available.

HU3500 - analog Humidity sensor only - can be proposed

FEATURES

- Full interchangeability with no calibration required in standard conditions
- Instantaneous desaturation after long periods in saturation phase
- Analog output
- Demonstrated reliability and long term stability
- Reliability not affected by repeated condensation
- HU3500 analog humidity sensor only can be proposed

APPLICATIONS

- Home appliance
- Medical
- Printers
- Humidifier



PERFORMANCE SPECS

MAXIMUM RATINGS

Ratings		Symbol	Value	Unit
Storage Temperature		T _{stg}	-40 to 125	°C
Supply Voltage (Deels)	HTU3533 products	V _{cc}	16V	V _{dc}
Supply vollage (Peak)	HTU3535 products	Vcc	16V	V _{dc}
Humidity Operating Range		RH	0 to 100	%RH
Temperature Operating Range		Ta	-40 to +85	°C
	HTU3533 products		-0.3 to 3.6V	V
VDD to GND	HTU3535 products		-16 to 16V	V
Input current on any pin			-10 to +10	mA

Peak conditions: less than 10% of the operating time

Exposure to absolute maximum rating conditions for extended periods may affect the sensor reliability.



OPERATING RANGE

ELECTRICAL AND GENERAL ITEMS

HTU35Y3

Characteristics	Symbol	Min	Тур	Max	Unit
Voltage Supply (1) (2)	Vcc	2.85	3.0	3.15	V _{dc}
Nominal Output @55%RH	Vout		1.490		V
Humidity Average Sensitivity	ΔmV/RH	-	+16	-	mV/%RH
Current consumption	Icc	-	1.0	1.2	mA dc

(1) Module is ratiometric to voltage supply
(2) Maximum power supply ramp up time to VCC should be less than 20ms

HTU35Y5

Characteristics	Symbol	Min	Тур	Max	Unit
Voltage Supply (1) (2)	V _{cc}	4.75	5	5.25	V _{dc}
Nominal Output @55%RH	Vout	2.401	2.480	2.559	V
Humidity Average Sensitivity	ΔmV/RH	-	+26	-	mV/%RH
Current consumption	Icc	-	1.2	1.5	mA dc

(1) Module is ratiometric to voltage supply

Maximum power supply ramp up time to VCC should be less than 20ms

SENSOR PERFORMANCE

ELECTRICAL CHARACTERISTICS

(@T=23°C, $R_L>1M\Omega$ unless otherwise noted)

Humidity Characteristics	Symbol	Min	Тур	Max	Unit
Humidity Measuring Range	RH	0		100	%RH
Relative Humidity Accuracy (20% to 80%RH)			±2	See graph	%RH
Temperature coefficient (10°C to 50°C)	T _{cc}			-0.15	%RH/°C
Recovery time after 150 hours of condensation	t		10		S
Humidity hysteresis			+/-1		%RH
Output impedance	Z			50	Ω
Sink current capability ($R_{L_{Min}} = 8 \text{ kOhms}$) ⁽¹⁾	I			1	mA
Warm up time (90% of signal)	tw		150		ms
Time Constant (at 63% of signal) 33%RH to 75%RH $^{\rm (2)}$	τ		5	10	S

(1) Conditions of sink current: Vout + 0.054V (3%RH) at Vout = 0.600 V (Vout min)

(2) At 1m/s air flow

Temperature Characteristics*	Symbol	Min	Тур	Max	Unit
Nominal resistance @ 25°C	R	9.9	10	10.1	kΩ
Beta value : B25/50	В	3346	3380	3414	K
Temperature measuring range	Ta	-40		+80	°C
Nominal Resistance Tolerance at 25°C	Rn		1		%
B value tolerance	В		1		%
Time Constant	т		10		S

* Except for low temperatures

POWER SUPPLY OPTION OF HTU3500 SERIES AT $3V_{DC}$ OR AT $5V_{DC}$

At $3V_{DC}$ or at $5V_{DC}$ power supply, there is no measurable impact of type of powering on temperature and RH accuracy.

HUMIDITY LOOK-UP TABLES

HTU3535 Modeled Voltage Output							
F	Reference Output Values (Vcc = 5V)						
0	Vout (mV)	RH (%)	Vout (mV)				
10	1235	55	2480				
15	1390	60	2605				
20	1540	65	2730				
25	1685	70	2860				
30	1825	75	2990				
35	1960	80	3125				
40	2090	85	3260				
45	2220	90	3400				
50	2350	95	3530				

POLYNOMIAL EQUATIONS

$$\begin{split} V_{out} &= 8.43 \overline{E^{-4}} \ RH^3 - 0.1485 \ RH^2 + 34.16 \ RH + 909 \\ RH &= -1.564 \overline{E^{-9}} V_{out}{}^3 + 1.205 \overline{E^{-5}} V_{out}{}^2 + 8.22 \overline{E^{-3}} V_{out} - 15.6 \\ & \ with \ V_{out} \ in \ mV \ and \ RH \ in \ \% \end{split}$$

LINEAR EQUATIONS

 $V_{out} = 26.23 \text{ RH} + 1032$ RH = 0.03812 $V_{out} - 39.36$ with V_{out} in mV and RH in %

Reference Output Values (Vcc = 3V) RH (%) Vout (mV) RH (%) Vout (mV) 10 740 55 1490 15 835 60 1565 20 65 925 1640 25 70 1010 1715 30 75 1095 1795 35 1175 80 1875 40 1255 85 1955 2040 45 1330 90 50 1410 95 2120

HTU3533 Modeled Voltage Output

POLYNOMIAL EQUATIONS

 $\begin{array}{l} V_{out} = 5.05 E^{-4} \; RH^3 - 8.91 \; E^{-2} \; RH^2 + 2.05 \; E^1 \; RH + 5.45 \; E^2 \\ RH = -7,23 \; E^{-9} V_{out}{}^3 + 3,34 \; E^{-5} V_{out}{}^2 + 1,37 \; E^{-2} V_{out} \; - 15.6 \\ with \; V_{out} \; in \; mV \; and \; RH \; in \; \% \end{array}$

LINEAR EQUATIONS

 $V_{out} = 15.94 \text{ RH} + 606$ RH = 0,0627 V_{out} - 37,969 with V_{out} in mV and RH in %

RELATIVE HUMIDITY ERROR BUDGET CONDITIONS AT 25°C



TEMPERATURE COEFFICIENT COMPENSATION EQUATION

For other temperatures than 25°C, the following temperature coefficient compensation equation can be used and will guarantee Relative Humidity accuracy given in table1, from 0°C to 80°C:

$$RH_{compensatedT} = RH_{actualT} + f(T)$$

RHactualTAmbient humidity in %RH, computed from HTU21D(F) sensorTactualHumidity cell temperature in °C, computed from HTU21D(F) sensorf(T)RH correction (in %RH) is a linear function of the temperature T (°C) as describedbelow:f(T) = -0.15 * (25 - T)

TEMPERATURE

Temperature Characteristics	Symbol	Min	Тур	Max	Unit
Nominal resistance @ 25°C	R	9.9	10	10.1	kΩ
Beta value : B25/50	В	3346	3380	3414	K
Temperature measuring range	Ta	-40		110	°C
Nominal Resistance Tolerance at 25°C	Rn		1		%
B value tolerance	В		1		%
Time Constant	т		10		S

TYPICAL TEMPERATURE OUTPUT

Depending on the needed temperature measurement range and associated accuracy, we suggest two methods to access to the NTC resistance values.

$$R_T = R_N \times e^{\beta \left(\frac{1}{T} - \frac{1}{T_N}\right)}$$

 R_T NTC resistance in Ω at temperature T in K

 R_N NTC resistance in Ω at rated temperature T in K

T, T_N Temperature in K

β Beta value, material specific constant of NTC

e Base of natural logarithm (e=2.71828)

 \bigcirc The exponential relation only roughly describes the actual characteristic of an NTC thermistor can, however, as the material parameter β in reality also depend on temperature. So this approach is suitable for describing a restricted range around the rated temperature or resistance with sufficient accuracy.

© For practical applications, a more precise description of the real R/T curve may be required. Either more complicated approaches (e.g. the Steinhart-Hart equation) are used or the resistance/temperature relation as given in tabulation form. The below table has been experimentally determined with utmost accuracy for temperature increments of 1 degree.

Actual values may also be influenced by inherent self-heating properties of NTCs. Please refer to MEAS-France Application Note HPC106 "Low power NTC measurement

TEMPERATURE LOOK-UP TABLE

Temp	R	Temp	R]	Temp	R]	Temp
(°C)	(Ω)	(°C)	(Ω)		(°C)	(Ω)		(°C)
-40	195652	0	27219		40	5834		80
-39	184917	1	26076		41	5636		81
-38	174845	2	24988		42	5445		82
-37	165391	3	23951		43	5262		83
-36	156513	4	22963		44	5086		84
-35	148171	5	22021		45	4917		85
-34	140330	6	21123		46	4754		86
-33	132958	7	20267		47	4597		87
-32	126022	8	19450		48	4446		88
-31	119494	9	18670		49	4301		89
-30	113347	10	17926		50	4161		90
-29	107565	11	17214		51	4026		91
-28	102116	12	16534		52	3896		92
-27	96978	13	15886		53	3771		93
-26	92132	14	15266		54	3651		94
-25	87559	15	14674		55	3535		95
-24	83242	16	14108		56	3423		96
-23	79166	17	13566		57	3315		97
-22	75316	18	13049		58	3211		98
-21	71677	19	12554		59	3111		99
-20	68237	20	12081		60	3014		100
-19	64991	21	11628		61	2922		101
-18	61919	22	11195		62	2834		102
-17	59011	23	10780		63	2748		103
-16	56258	24	10382		64	2666		104
-15	53650	25	10000		65	2586		105
-14	51178	26	9634		66	2509		106
-13	48835	27	9284		67	2435		107
-12	46613	28	8947		68	2364		108
-11	44506	29	8624		69	2294		109
-10	42506	30	8315		70	2228		110
-9	40600	31	8018		71	2163		
-8	38791	32	7734		72	2100		
-7	37073	33	7461		73	2040		
-6	35442	34	7199		74	1981		
-5	33892	35	6948		75	1925		
-4	32420	36	6707		76	1870		
-3	31020	37	6475		77	1817		
-2	29689	38	6253		78	1766		
-1	28423	39	6039		79	1716		

TEMPERATURE ERROR BUDGET



0.1°C tolerance on Resistance Measurement

STEINHART-HART COEFFICIENTS

According to the equation below, the Steinhart-Hart coefficients for the operating temperature range for HTU3500 products thermistor are:

$$\frac{1}{T} = a + b * \ln(R) + C * \ln(R) * \ln(R) * \ln(R)$$

R NTC resistance in Ω at temperature T in K

- T Temperature in K
- a Constant value (a= 8.61393E-04)
- b Constant value (b= 2.56377E-04)
- c Constant value (c= 1.68055E-07)

TEMPERATURE INTERFACE CIRCUIT

Concerning the temperature sensor of the HTU3500 Series products, the following measuring method described below is based on a voltage bridge divider circuit. It uses only one resistor component (Rbatch) at 1% to design HTU3500 temperature sensor interfacing circuit.

Rbatch is chosen to be equal to NTC @25°C to get: Vout = Vcc/2 @25°C.

The proposal method connects Rbatch to Vcc and NTC to Ground. It leads to a negative slope characteristic (Pull-Up Configuration).



$$V_{OUT}(mV) = \frac{Vcc(mV) * NTC_{HTU3500}(\Omega)}{R_{batch}(\Omega) + NTC_{HTU3500}(\Omega)}$$

		For HTU3533 products (VCC=3VDC)	For HTU3535 products (VCC=5VDC)
Temperature (°C)	Resistance (Ω)	Pull-Up Configuration Vout (mV)	Pull-Up Configuration Vout (mV)
-40	195652	2854	4757
-30	113347	2757	4595
-20	68237	2617	4361
-10	42506	2429	4048
0	27219	2194	3657
10	17926	1926	3210
20	12081	1641	2736
25	10000	1500	2500
30	8315	1362	2270
40	5834	1105	1842
50	4161	882	1469
60	3014	695	1158
70	2228	547	911
80	1669	429	665
85	1452	380	634

• Storage Conditions and Handling Instructions

It is recommended to store HTU3500 Series sensor in its original packaging at following conditions: Temperature shall be in the range of $-40^{\circ}C - 125^{\circ}C$

APPLICATION: DEW POINT TEMPERATURE MEASUREMENT

The **dew point** is the temperature at which the water vapor in the air becomes saturated and condensation begins.

The dew point is associated with relative humidity. A high relative humidity indicates that the dew point is closer to the current air temperature. Relative humidity of 100% indicates that the dew point is equal to the current temperature (and the air is maximally saturated with water). When the dew point stays constant and temperature increases, relative humidity will decrease.

Dew point temperature of the air is calculated using Ambient Relative Humidity and Temperature measurements from HTU3500 Series sensor with following formulas given below

Partial Pressure (PP_{Tamb}) formula from Ambient Temperature:

$$PP_{Tamb} = 10^{\left[A - \frac{B}{(Tamb + C)}\right]}$$

Dew point Temperature (T_d) formula from Partial Pressure (PP_{Tamb}):

$$T_{d} = -\left[\frac{B}{\log_{10}\left(RH_{amb} \times \frac{PP_{Tamb}}{100}\right) - A} + C\right]$$

PPTamb	Partial Pressure in mmHg at ambient temperature (T _{amb})
RH _{amb}	Ambient humidity in %RH, computed from HTU3500 Series sensor
T _{amb}	Humidity cell temperature in °C, computed from HTU3500 Series sensor
Td	Calculated Dew Point in °C
A, B, C	Constants: A=8.1332; B=1762.39; C=235.66

CONNECTING AND MECHANICAL CHARACTERISTRICS

CONNECTING CHARACTERISTICS

Connector Type*	Symbol	Overview	Connector Pitch	Mating Connector
Medium Male Connector ^{(1) (2)} (1.91 mm – 0.075 in long)	PVBM	1 8 1 3 5 1 5 1 5 1 5 1 5 1 5 1 5 1 5 1 5 1	(2,00) .0787 (2,00) .0787 (2,00) .0787 .0787 .0787 .0787 .0787	Direct Soldering (through hole)

* For alternate connector type, please contact factory.

⁽¹⁾ For board-to-board mounting, we suggest wave soldering.

⁽²⁾ Pins are connected by twos.

Pin Out Assignment				
N°	Function			
1/8	Ground			
2/7	Vcc – Voltage Supply			
3/6	Tout – Temperature			
4/5	RHout – Relative Humidity			

WIRING CHARACTERISTICS

Connector Type	Symbol	Overview	More information*	Remote Mating Connector*
N/A	WxxGyy	A TO MARK A A	Wxx: Wiring cable length* in mm Gyy: Wiring cable type* (from AWG 24 to 30):	N/A

* On request, please contact factory.

N°	Colour	Function	
1	Black	Ground	
2	Red	Vcc – Voltage Supply	
3	Brown	Tout – Temperature	
4	Yellow	RHout – Relative Humidity	

Pin Out Assignment (with wires)

RESISTANCE TO PHYSICAL AND CHEMICAL STRESSES

HTU3500 series modules have been tested according to table below:

Environment	Standard	Results
Salt atmosphere	JESD22-A107-A	Within specification
Temperature cycling	-20°C / +85°C, 168 hours	Within specification
Thermal shocks	-20°C / +85°C, 500 cycles	Within specification
High temperature / Humidity operating life	93%RH / +60°C, 168 hours	Within specification
Resistance to immersion into water	Ambient temperature	Within specification
Low temperature storage	-20°C, 500 hours	Within specification
High temperature storage	+85°C, 500 hours	Within specification
ESD immunity	JEDEC JESD22-A114 JEDEC JESD22-A115	Within specification* Within specification**

 * JEDEC JESD22-A114 method for connections & open window (Human Body Model at $\pm 8kV$ powered and unpowered)

**JEDEC JESD22-A115 method (Machine Model ±200V)

HTU3500 Series are protected against reverse polarity.

HTU3500 Series are not light sensitive

ENVIRONMENTAL AND RECYCLING

HTU3500 series modules are lead free components and are compatible with Pb Free soldering process.

HTU3500 series modules are free from Cr (6+), Cd and Hg.

PACKAGE OUTLINE

MECHANICAL CHARACTERISTICS: HTU3500 SERIES PACKAGE OUTLINE



Double coated adhesive tape could be used on plastic housing area (ref: 3M - 5925F) to fix parts

ORDERING INFORMATION

Product	Order Reference	Status
HTU3515WXGY	HPP831NXXX	In design
HTU3535WXGY	HPP831CXXX	Engineering part
HTU3535PBVM	HPP831A610	Serial part
HTU3535CH	HPP831AXXX	In design

Samples are available through MEASUREMENT SPECIALTIES web site:

http://www.meas-spec.com/humidity-sensors.aspx

EUROPE

Measurement Specialties, Inc - MEAS France Impasse Jeanne Benozzi CS 83 163 31027 Toulouse Cedex 3 FRANCE Tél: +33 (0)5 820 822 02 Fax: +33(0)5 820 821 51 Sales: humidity.sales@meas-spec.com

TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.