

REV. 1 9/12/97

COIL: @ 25°C

RESISTANCE 98 OHMS ± 10%

NOMINAL VOLTAGE 6.0 VDC

MUST OPERATE 3.5 VDC

MUST RELEASE 2.0 VDC MAX, 0.28 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX

RELEASE TIME 1.5 MS MAX

CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 10/23/95 *CK ZERON 9/12/97*

COMMUNICATIONS INSTRUMENTS, INC.

CUST. OPL
CUST. NO. M39016/17-038M

TYPE "JMGA" RELAY

JMGAC-6MW