


REV. 0
DCO 143384

COIL: @ 25°C	
RESISTANCE	390 OHMS ±10%
NOMINAL VOLTAGE	12.0 VDC
MUST OPERATE	7.0 VDC
MUST RELEASE	4.0 VDC MAX, 0.63 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 Hz TO 3000 Hz @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C
NOTES: OPERATE TIME 2.0 MS MAX	
RELEASE TIME 4.0 MS MAX	
CONTACT STABILIZATION 2.5 MS MAX	

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS

DR. HDS 1/14/02 *[Signature]* 1/14/02

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/18-040P REV.

"JMGAD" RELAY

JMGACD-12PW