



MEDIUM VOLTAGE CONDUCTOR COVER (MVCC) WILDLIFE AND ASSET PROTECTION PRODUCTS

KEY FEATURES

- Superior tracking resistance
- Protection for leads and jumpers
- Simple, quick, tool free and wrap around installation

TE Connectivity's (TE) Raychem medium voltage conductor covers (MVCC) provide high quality electrical insulation for substation leads and jumpers. These covers are made from a non-tracking silicone material that is suitable for harsh medium voltage outdoor environments. TE's Raychem MVCC covers are split for easy installation.

MVCC is suitable for applications up to 25 kV phase to ground. Currently, four sizes are available and will fit conductors with diameters up to 44 mm (1.75"). The flexibility of the covers allows for installation on tight bends which is ideal for substation applications. Covers are designed to protect energized conductors from flashovers due to contact from birds and animals.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.

Medium Voltage Conductor Cover MVCC



TE's wildlife and asset protection products and systems of tubes, tapes, sheets, pre-formed covers and barriers provide a proven, cost-effective and easy-to-install solution to bird, animal and weather related outages.

PRODUCT PERFORMANCE			
Test			
AC Dry Withstand/1 min.	35 kV Line Voltage (all three phase covered) 25 kV Line Voltage (all three phases covered) 25 kV phase-to-ground 15 kV phase-to-ground		
Loading Cycleing 30 days at 130°C	No Deformation or Splitting		
Low Temperature Install at 0°C	Installable without Difficulty		
Physical			
Key Material Properties	Test Method	Results	
Accelerated Aging 168 hrs. 150°C Tensile Strength	ASTM D412	> 1.3 MPa (psi)	
Accelerated Aging 168 hrs. 150°C Ultimate Elongation	ASTM D412	90% min.	
Low Temperature Flexibility 4 hrs.- 20°C	ASTM D2671	No Cracking	
Electrical			
Dielectric Strength 1.91 mm thickness	ASTM D149	> 120 kV/cm (300 V/mil)	
Tracking and Erosion Resistance	ASTM D2303	No tracking or erosion to top surface or flame failure after: 1 hr. at 2.5 kV 1 hr. at 2.75 kV 1 hr. at 3.0 kV 20 min at 3.25 kV	
Volume Resistivity	ASTM D257	1 x 10 ¹³ Ohm cm min.	
Selection			
Description	Use Range UOM: mm (Inches)	Color	Supplied Length UOM: M (Feet)
MVCC-10/.40 (S30)	Up to 11 (0.45)	Red	2 pieces at 15 (50)
MVCC-G-10/.40 (S30)	Up to 11 (0.45)	Grey	2 pieces at 15 (50)
MVCC-19/.75 (S15)	11 (0.45) - 19 (0.75)	Red	2 pieces at 7.5 (25)
MVCC-G-19/.75 (S15)	11 (0.45) - 19 (0.75)	Grey	2 pieces at 7.5 (25)
MVCC-25/1.0 (S7)	19 (0.75) - 28 (1.125)	Red	1 piece at 7.0 (25)
MVCC-G-25/1.0 (S7)	19 (0.75) - 28 (1.125)	Grey	1 piece at 7.0 (25)
MVCC-45/1.75 x 4 (S7)	28 (1.125) - 44 (1.75)	Red	6 pieces at 1.2 (4)
MVCC-G-45/1.75 x 4 (S7)	28 (1.125) - 44 (1.75)	Grey	6 pieces at 1.2 (4)

TECHNICAL REPORT	
EDR-5498	Medium Voltage Conductor Cover (MVCC) Material Test Report
EDR-5461	Medium Voltage Conductor Cover (MVCC) Product Test Report

INSTALLATION INSTRUCTIONS	
PII 55790	Installation Instructions for Medium Voltage Conductor Cover (MVCC)

te.com/energy

© 2018 TE Connectivity. All Rights Reserved. EPP-2605-7/18

Raychem, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and Company names mentioned herein may be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Technical Support Centers

USA:	+ 1 800 327 6996
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Italy:	+ 39 333 250 0915
Benelux:	+ 32 16 508 695
Russia:	+ 7 495-790 790 2-200
China:	+ 86 (0) 400-820-6015