


.017 ^{+0.002}/_{-.001} DIA.
9 PINS

COIL: @ 25°C

RESISTANCE	1560 OHMS ± 10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	14.2 VDC
GATE TURN-ON	4.3 VDC MAX.
GATE TURN-OFF	0.5 VDC MAX.
MUST RELEASE	8.0 VDC MAX, 1.30 VDC MIN.

CUSTOMER DATA SHEET




ENVIRONMENT:

VIBRATION	10	CPS TO	3000	CPS @	30	g's
SHOCK	75	g's	6	MS. DURATION		
TEMPERATURE	-65	°C TO	+125	°C		

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

NOTES: OPERATE TIME 2.5 MS MAX.
RELEASE TIME 4.0 MS MAX.
CONTACT STABILIZATION 2.0 MS MAX.

DR. R.B. 9/3/98 *[Signature]* 9/3/98



CUST. QPL
CUST. NO. M28776/6-012M

TYPE JMGAT RELAY

JMGAT-26MW