


COIL: @ 25°C
 RESISTANCE 3200 OHMS ± 10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 14.0 VDC
 MUST RELEASE 8.0 VDC MAX, 1.4 VDC MIN.

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX
RELEASE TIME 2.5 MS MAX
CONTACT TIME 1.5 MS MAX
TESTED TO MIL-R-39016, LEVEL L

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS MIN

DR. R.B. 10/5/95 CK. 10/5/95

COMMUNICATIONS INSTRUMENTS, INC.

CUST. QPL
 CUST. NO. M39016/41-044L

TYPE JMGS RELAY

JMGSP-26L