


REV. 0  
DCO 143202

COIL: @ 25°C  
RESISTANCE 1600 OHMS ±10%  
NOMINAL VOLTAGE 18.0 VDC  
MUST OPERATE 9.8 VDC  
MUST RELEASE 6.0 VDC MAX., 0.92 VDC MIN.

ENVIRONMENT:  
VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
SHOCK 75 g's 6 MS. DURATION  
TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX.  
RELEASE TIME 2.0 MS MAX.  
CONTACT STABILIZATION TIME 2.0 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO  
1A 28 VDC RESISTIVE 100,000  
OPERATIONS

DR. ASB 9/07/01

*OK* 9/7/01

**AICII Technologies**  
advanced control electronic solutions

CUST. QPL  
CUST. NO. M39016/11-048P REV.

"JMS" RELAY

JMSC-18XPS