

# **HEAT SHRINKABLE TUBING** FLEXIBLE, FLAME-RETARDANT,GENERAL PURPOSE, POLYOLEFIN TUBING

### **KEY FEATURES**

- 2:1 shrink ratio
- Superior abrasion and solvent resistance when compared with that of many flexible, general purpose polyolefin tubings
- Excellent physical,chemical, and electrical properties that meet or exceed industrial and military standards for highly reliable, general purpose tubing
- Flexible; conforms to irregular shapes
- Flame-retardant (colors only)
- Wide range of sizes and colors
- RoHS compliant

TE Connectivity's (TE) Raychem Designed to provide superior mechanical (abrasion, cut through, and strain relief), thermal, and fluidresistance performance in demanding environments.

Widely used to provide insulation and strain relief of wire terminations and connections. Used for jacketing wire bundles and light-duty harnesses where superior abrasion resistance is a plus. Also used to identify and color code electrical connections and wire bundles.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.







# DIMENSIONS

	Inside D	Recovered Wall Thickness**	
Size	Minimum Expanded as Supplied	Maximum Recovered After Heating	After Heating
3/64	1.2 (0.046)	0.6 (0.023)	0.40 ± 0.08 (0.016 ± 0.003)
1/16	1.6 (0.063)	0.8 (0.031)	0.43 ± 0.08 (0.017 ± 0.003)
3/32	2.4 (0.093)	1.2 (0.046)	0.51 ± 0.08 (0.020 ± 0.003)
1/8	3.2 (0.125)	1.6 (0.062)	0.51 ± 0.08 (0.020 ± 0.003)
3/16	4.8 (0.187)	2.4 (0.093)	0.51 ± 0.08 (0.020 ± 0.003)
1/4	6.4 (0.250)	3.2 (0.125)	0.64 ± 0.08 (0.025 ± 0.003)
3/8	9.5 (0.375)	4.8 (0.187)	0.64 ± 0.08 (0.025 ± 0.003)
1/2	12.7 (0.500)	6.4 (0.250)	0.64 ± 0.08 (0.025 ± 0.003)
3/4	19.1 (0.750)	9.5 (0.375)	0.76 ± 0.08 (0.030 ± 0.003)
1	25.4 (1.000)	12.7 (0.500)	0.89 ± 0.12 (0.035 ± 0.005)
1 1/4	31.8 (1.250)	15.9 (0.625)	1.02 ± 0.15 (0.040 ± 0.006)
1 1/2	38.1 (1.500)	19.1 (0.750)	1.02 ± 0.15 (0.040 ± 0.006)
2	50.8 (2.000)	25.4 (1.000)	1.14 ± 0.16 (0.045 ± 0.007)
3	76.2 (3.000)	38.1 (1.500)	1.27 ± 0.20 (0.050 ± 0.008)
4	101.6 (4.000)	50.8 (2.000)	1.40 ± 0.23 (0.055 ± 0.009)
5	127.0 (5.000)	63.5 (2.500)	1.52 ± 0.23 (0.060 ± 0.009)

\*\*Wall thickness will be less if tubing recovery is restricted during shrinkage.

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

# ORDERING INFORMATION

ORDERING INFORMATION				
Color	Standard	Black (-0, BK), white (-9, WH), red (-2, RD), blue (-6, BU), yellow (-4, YO), clear (-X, CL)		
Color	Nonstandard	Brown (-1, BN), orange (-3, OR), green (-5, GN), violet (-7, VT), gray (-8, GY)		
Size selection	Always order the largest size that will shrink snugly over the component to be covered. Special order sizes are available upon request.			
Standard packaging***	On spools or in 1.2-meter [4-foot] lengths.			
Ordering description****	Specify product name, size and color (for	example, RNF-100 1/4-0 [Europe] or RNF-100 1/4-BK [Americas].		

\*\*\*\*Available in the convenient Mini-Spool packaging/dispensing system, for sizes 3/64" up to 1".

\*\*\*\*Europe only. For supply to MIL, Def Stan and BS add -MS, -DS or -BS to ordering description.

### te.com/energy

© 2019 TE Connectivity. All Rights Reserved. EPP-3382-DDS-6/19-HS-TUBING-TE

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

#### FOR MORE INFORMATION: TE Technical Support Centers

USA: Canada: Mexico: Latin/S. America: France: UK: Germany: Spain: Italy: Benelux:

Russia:

China:

+1800 327 6996
+1(905)475-6222
+ 52 (0) 55-1106-0800
+ 54 (0) 11-4733-2200
+ 33 380 583 200
+ 44 0870 870 7500
+ 49 896 089 903
+ 34 916 630 400
+ 39 333 250 0915
+ 32 16 508 695
+ 7 495-790 790 2-200

+ 86 (0) 400-820-6015

