

te.com



HORIZONTAL SHORT-SWING LIQUID LEVEL SENSORS

LDS Series

High- or low-level switching

N.O./N.C. SPST output

Mounted on the side wall of a tank

Certified reed switch (UL component listed)

Body and float made from glass filled nylon 6.6

Features

- · Voltage rating up to 250VAC
- Current rating up to 1.0 amp
- · Compact design and low profile
- Optional cable lengths
- Includes mounting hardware
- Full and/or empty detection

Applications

- Water and fuel storage tanks
- Pump on/off controls
- · Marine bilge and ballast tanks
- Flood detection and prevention
- · Coolant level indication
- Livestock watering tanks
- Irrigation systems
- · Water treatment plants
- Waste water tanks
- Chemical storage and processing

The LDS series of point liquid level switches demonstrates a high degree of reliability due to the use of non-reactive wetted components and a unique reed switch designed specifically for level sensing applications. The sensor utilizes a moving float with an embedded magnet to activate a reed switch located in the sensor body. As the liquid level raises the float, it moves a magnet into close proximity of the reed switch and actuates it to give an open contact or closed contact switch indication.

The reliability of this sensor results from a very simple operating principle, a single moving part, media compatible wetted materials, and a unique reed switch design that has a UL recognized component certification.

The sensor mounts into the side wall of a liquid storage tank using an M16 x 2.0 threaded fitting. The M16 mount is available in an internal or external configuration. The output is a simple N.O. or N.C. SPST reed switch that utilizes Ruthenium contact points for reliability. Changing from a N.O. output to a N.C. output is done by rotating the switch 180° in the mounting hole. This change can be done in the field. Electrical outputs are a single pair of wires with PVC insulation and optional lengths of $0.5~\mathrm{m}$ or $2.0~\mathrm{m}$.

CLICK HERE > CONNECT WITH A SPECIALIST

Absolute Maximum Ratings (1)


Parameter	Min	Max	Units	Notes/Conditions
DC contact voltage (SPST)		200	V	
DC contact current (SPST)		1.0	Α	Do not exceed 70W
RMS contact voltage (SPST)		250	V	
RMS contact current (SPST)		1.0	Α	
Storage and operating temperature	-30	105	°C	
Fitting pressure	-1.0	4.7	Bar	Internal tank pressure
Tank wall thickness (Internal mount)	1.0	10	mm	
Tank wall thickness(External mount)	1.0	4.0	mm	

⁽¹⁾ Maximum limits the device will withstand without damage

Product Specifications

Parameter	Details & Options			
Mounting Orientation	Side entry			
Fitting	M16 x 2.0 Internal or External			
Switch Operation	N.C. when float is horizontal			
Contact Forms	Form A (SPST)			
Contact Material	Ruthenium			
Contact resistance (max)	140 mΩ			
Housing and Float Material	Glass filled nylon 6.6 (better for oil, fuel, non-ionic liquids) Glass filled Polypropylene (better for water and aqueous solutions)			
Cable Description	18 AWG 32/0.2mm PVC insulated, UL/CSA/BS6361			
Shock	±50g 11ms half sign duration			
Vibration	±35g 0 – 500Hz			
Ambient Humidity	0 – 95% RH (non-condensing)			
Ingress protection	IP68 (wetted surfaces) IP65 (non-wetted surfaces)			
Approvals & Certifications	UL file E98428			

Outline Dimensions




Schematic




Switch position with no magnet present

Mounting Orientations



Mounting Detail & Hardware




M16 SENSOR FITTING

ASSEMBLED VIEW

LDS Series

Ordering Information



CLICK HERE > CONNECT WITH A SPECIALIST

NORTH AMERICA

Tel +1 800 522 6752

EUROPE

Tel +31 73 624 6999

ASIA

Tel +86 0400 820 6015

te.com/sensors

TE Connectivity, TE, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2020 TE Connectivity Corporation. All Rights Reserved.

10/2020