




SUSPENSION INSULATOR

HIGH CREEPAGE COMPOSITE SUSPENSION INSULATOR

KEY FEATURES

- 70kN tension rating (SML)
- Wide selection of metal end fittings selection
- Reliable tensile performance
- Light-weight for easier installation
- Shed design to minimize insulator length per kV rating
- Shock and vibration resistant
- Good tracking and erosion resistance performance
- Quality design and manufactured in accordance with ISO9001


TE Connectivity (TE) offers a complete range of silicone suspension / tension insulators for overhead line applications up to 485 kV BIL.

Our complete portfolio of insulators is designed to fit a wide selection of metal end fittings. The portfolio includes numerous lengths and creepage configurations to fit the requirements of your application. TE's compact insulator profile has the same shed diameter to maximize flashover performance in polluted environments over a minimum insulator length.

Our suspension / tension insulators are made of silicone, a hydrophobic material with proven tracking and erosion resistance and high technical performance in a wide range of climatic and pollution conditions.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.

Suspension Insulator



Top Fitting - Socket Fitting per IEC 120-16A (Cast)
Bottom Fitting - Socket Fitting per IEC 120-16A (Cast)
R Clip - SS 304
SML - 70 kN
Routine Test - 35 kN

Part description key

CS - Composite Suspension
XX - SML Top/Bottom End Fittings
XXX - BIL (kV)
XXXX - Creepage distance (mm)
X - Mfg. Style
XX - Special Code

PRODUCT SPECIFICATION

TCPN	DESCRIPTION	NOMINAL CREEPAGE (mm)	NOMINAL DRY ARC (mm)	DRY AC WITH-STAND (kV)	WET AC WITH-STAND (kV)	DRY AC FLASH-OVER (kV)	WET AC FLASH-OVER (kV)	LIGHT-NING IMPULSE WITH-STAND (kV)	LIGHT-NING IMPULSE FLASH-OVER (kV)	A (mm)	B (mm)
EN9616-000	CS-70-SS-100-0265-M-01	265	125	60	45	75	60	100	115	258	60
EN9617-000	CS-70-SS-115-0355-M-01	355	155	70	55	86	70	115	130	288	90
EN9618-000	CS-70-SS-130-0445-M-01	445	185	85	65	95	80	130	145	318	120
EN9619-000	CS-70-SS-145-0535-M-01	535	215	90	70	105	85	145	160	348	150
EN9620-000	CS-70-SS-165-0625-M-01	625	245	100	80	115	100	165	175	378	180
EN9621-000	CS-70-SS-180-0715-M-01	715	275	115	90	125	105	180	195	408	210
EN9622-000	CS-70-SS-200-0805-M-01	805	305	125	100	135	115	200	210	438	240
EN9623-000	CS-70-SS-215-0895-M-01	895	335	135	110	145	125	215	225	468	270
EN9624-000	CS-70-SS-230-0985-M-01	985	365	145	120	155	135	230	240	498	300
EN9625-000	CS-70-SS-245-1075-M-01	1075	395	155	130	165	145	245	255	528	330
EN9626-000	CS-70-SS-260-1165-M-01	1165	425	165	140	175	155	260	275	558	360
EN9627-000	CS-70-SS-275-1255-M-01	1255	455	175	145	185	165	275	290	588	390
EN9628-000	CS-70-SS-290-1345-M-01	1345	485	185	155	195	175	290	305	618	420
EN9629-000	CS-70-SS-310-1435-M-01	1435	515	195	165	205	180	310	320	648	450
EN9630-000	CS-70-SS-325-1525-M-01	1525	545	205	175	215	190	325	335	678	480
EN9631-000	CS-70-SS-340-1615-M-01	1615	575	215	185	225	200	340	350	708	510
EN9632-000	CS-70-SS-355-1705-M-01	1705	605	225	195	235	210	355	365	738	540
EN9633-000	CS-70-SS-370-1795-M-01	1795	635	235	200	245	220	370	385	768	570
EN9634-000	CS-70-SS-390-1885-M-01	1885	665	245	210	255	230	390	400	798	600
EN9635-000	CS-70-SS-405-1975-M-01	1975	695	255	220	265	240	405	415	828	630
EN9636-000	CS-70-SS-420-2065-M-01	2065	725	265	230	275	250	420	430	858	660
EN9637-000	CS-70-SS-435-2155-M-01	2155	755	280	240	285	260	435	445	888	690
EN9638-000	CS-70-SS-450-2245-M-01	2245	785	290	250	295	270	450	460	918	720
EN9639-000	CS-70-SS-470-2335-M-01	2335	815	300	260	305	275	470	475	948	750
EN9640-000	CS-70-SS-485-2425-M-01	2425	845	310	265	315	285	485	490	978	780

FOR MORE INFORMATION: TE Technical Support Centers

USA: +1 800 327 6996
France: +33 380 583 200
UK: +44 0870 870 7500
Germany: +49 896 089 903
Spain: +34 916 630 400
Italy: +39 333 250 0915
Benelux: +32 16 351 731
Canada: +1 (905) 475-6222
Mexico: +52 (0) 55-1106-0800
Latin/S. America: +54 (0) 11-4733-2200
China: +86 (0) 400-820-6015

te.com/energy

©2020 TE Connectivity Ltd. All Rights Reserved. EPP-3469-DDS-1/2020

Raychem, TE Connectivity and TE Connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.