


REV. 1 3/23/99
DCO 140960

COIL: @ 25°C	
RESISTANCE	50 OHMS \pm 10%
NOMINAL VOLTAGE	5.0 VDC
MUST OPERATE	2.7 VDC
MUST RELEASE	0.22 VDC

ENVIRONMENT:	
VIBRATION	10 CPS TO 3000 CPS @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES:	OPERATE TIME 2.0 MS MAX
	RELEASE TIME 1.5 MS MAX
	CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1 AMP
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 10/3/97 *[Signature]* 3-23-99

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. C.I.I. STD.
CUST. NO.

TYPE 'MGA' RELAY

MGAC-5