


REV. 2 3/23/99  
DCO 140960

COIL:	② 25°C
RESISTANCE	98 OHMS $\pm$ 10%
NOMINAL VOLTAGE	6.0 VDC
MUST OPERATE	3.5 VDC
MUST RELEASE	.28 VDC

ENVIRONMENT:	
VIBRATION	10 CPS TO 3000 CPS @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES:	OPERATE TIME 2.0 MS MAX
	RELEASE TIME 1.5 MS MAX
	CONTACT BOUNCE 1.5 MS MAX

### CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1 AMP  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 9/28/95 [Signature] 3-23-99

**COMMUNICATIONS INSTRUMENTS, INC.**

CUST. C.I.I. STD.  
CUST. NO.

TYPE MGA RELAY

**MGAC-6W**