



MT-LWA

MODIFIED POLYOLEFIN HEAT SHRINK TUBING

PROFILE

- Shrink ratio $\leq 4:1$
- Full recovery at 110°C (230°F) minimum
- PFAS-free
- Custom sizing, finishing options available
- Radiopacity can be customized
- Adhesive-layer option available
- Translucent for high optical clarity

ABOUT

- MT-LWA is a crosslinked modified polyolefin heat shrink tubing designed for use as a process aid in minimally invasive applications
- Its homogeneous structure (properties evenly distributed) contributes to its consistency and high performance, making our MT-LWA essentially free from flaws, defects, pinholes, seams, cracks or inclusions
- MT-LWA offers customizable compressions strengths, shrink ratios $\leq 4:1$, is peelable with axial tear propagation and you can remove it while its warm, making it an excellent choice for reflowing catheter shafts when FEP isn't suitable

HEAT SHRINK TUBING — MT-LWA

TABLE 1: 2:1 EXPANSION RATIO DIMENSIONS (±)

Standard Sizes	As Supplied		Recovered			
	Inside Diameter Minimum (D)		Inside Diameter Maximum (d)		Wall Thickness (W)	
Size	in.	mm.	in.	mm.	in.	mm.
1/32	0.040 ± 0.005	1.02 ± 0.13	0.013 ± 0.002	0.33 ± 0.05	0.010 ± 0.002	0.25 ± 0.05
3/64	0.055 ± 0.005	1.40 ± 0.13	0.020 ± 0.003	0.51 ± 0.08	0.016 ± 0.003	0.41 ± 0.08
1/16	0.072 ± 0.005	1.83 ± 0.13	0.027 ± 0.004	0.69 ± 0.10	0.017 ± 0.003	0.43 ± 0.08
3/32	0.107 ± 0.008	2.72 ± 0.20	0.042 ± 0.004	1.07 ± 0.10	0.020 ± 0.003	0.51 ± 0.08
1/8	0.140 ± 0.010	3.56 ± 0.25	0.057 ± 0.005	1.45 ± 0.13	0.020 ± 0.003	0.51 ± 0.08
3/16	0.205 ± 0.010	5.21 ± 0.25	0.086 ± 0.007	2.18 ± 0.18	0.020 ± 0.003	0.51 ± 0.08
1/4	0.275 ± 0.015	6.99 ± 0.38	0.117 ± 0.008	2.97 ± 0.20	0.025 ± 0.003	0.64 ± 0.08
3/8	0.415 ± 0.020	10.54 ± 0.51	0.171 ± 0.016	4.34 ± 0.41	0.025 ± 0.003	0.64 ± 0.08

TABLE 2: 3:1 EXPANSION RATIO DIMENSIONS (MIN./MAX)

Standard Sizes	As Supplied		Recovered			
	Inside Diameter Minimum (D)		Inside Diameter Maximum (d)		Wall Thickness (W)	
Size	in.	mm.	in.	mm.	in.	mm.
.032	0.032	0.81	0.011	0.28	0.010 ± 0.002	0.25 ± 0.05
.047	0.047	1.19	0.013	0.33	0.012 ± 0.002	0.31 ± 0.05
.063	0.063	1.60	0.021	0.53	0.016 ± 0.002	0.41 ± 0.05
.078	0.078	1.98	0.025	0.64	0.016 ± 0.002	0.41 ± 0.05
.094	0.094	2.39	0.031	0.79	0.020 ± 0.003	0.51 ± 0.08
.110	0.110	2.79	0.034	0.86	0.020 ± 0.003	0.51 ± 0.08
.125	0.125	3.18	0.042	1.07	0.020 ± 0.003	0.51 ± 0.08
.188	0.188	4.78	0.063	1.60	0.020 ± 0.003	0.51 ± 0.08
.250	0.250	6.35	0.083	2.11	0.025 ± 0.003	0.64 ± 0.08
.375	0.375	9.53	0.125	3.18	0.025 ± 0.003	0.64 ± 0.08

HEAT SHRINK TUBING — MT-LWA

TABLE 3: PROPERTIES

Property	Unit	Requirement	Test Method
Physical			
Dimensions*	inches (mm)	In accordance with Table 1	
Longitudinal change*	percent	+0, -10 maximum	ASTM D 2671
Concentricity as supplied*	percent	70 minimum (2:1 Exp. ratio) 60 minimum (3:1 Exp. ratio)	ASTM D 2671
Tensile strength*	psi (MPa)	1500 minimum (10:3)	ASTM D 2671, 20"/minute
Ultimate elongation*	percent	200 minimum	
Secant modulus* (expanded)	psi (MPa)	2.5 x 10 ⁴ maximum (172)	ASTM D 2671
Heat resistance 168 hours at 175°C (347°F) Followed by test for: Ultimate elongation			
	percent	100 minimum	ASTM D 2671, 20"/minute
Electrical			
Dielectric strength	kV/mm	500 minimum (19.7)	ASTM D 2671
Dielectric			
withstand 3000V, 60Hz	sec	60 minimum	ASTM D 2671
Chemical			
Fluid resistance 24 hours at 23 ± 3°C (77 ± 5°F) Isopropyl alcohol 5% saline solution Disinfectant			ASTM D 2671
Followed by tests for: Dielectric strength	kV/mm	400 minimum (15.7)	ASTM D 2671
Tensile strength	psi (MPa)	1000 minimum (6.9)	ASTM D 2671
Heavy metals analysis Cadmium, Mercury, Lead, Bismuth, Antimony	ppm	1 maximum (total of all metals)	USP XXII Physiochemical tests-plastic (Note 1)

*Denotes lot acceptance test

Note 1: Sample preparation and extraction is per USP XXII. Metals analysis may be colorimetric as described in USP XXII or by equivalent quantitative analytical method.

TE.com/medical

TE Connectivity, TE connectivity (logo), Raychem and TE are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

© 2024 TE Connectivity. All Rights Reserved.

11/24 med-mt-lwa-hst-ss-en