

ES2000

Flame-retardant, adhesive-lined heat-shrinkable tubing (extended temperature range)

Adhesive-lined ES2000 heatshrinkable tubing is specifically designed to meet automotive industry requirements for environmental sealing and electrical insulation of automotive wire splices, terminations, and components.

ES2000 tubing has an outer jacket of radiation-crosslinked, semirigid polyolefin. Flame-retardant and mechanically tough, the jacket provides strain relief and abrasion protection of wire splices and mechanically sensitive components. The inner layer of the tubing is a unique hot-melt adhesive, specially formulated to adhere to all major types of automotive wire insulation and to perform well at an extended temperature range. The adhesive forms an effective barrier against automotive fluids and moisture, helping to protect the harness from the effects of corrosion and water wicking. Because ES2000 tubing has a high shrink ratio, only a few sizes are needed to cover a wide range of splice and component diameters. ES2000 tubing dimensions have been engineered to provide low-cost sealing solutions on multiple-wire splices (up to seven wires per side), using standard Tyco Electronics application equipment.

Temperature rating

Full recovery temperature:	135°C	
Continuous operating temperature:	-40°C to 130°C	

Specifications*

Туре	Raychem	UL	
ES2000	RT-1112	E85381	
*When ordering, always s	pecify latest issue.		

Dimensions (millimeters/inches)



	Inside	Inside diameter (including core)			Recovered wall thickness**						
	D (min	.)	d (ma	x.)	W		W1		W2		
	Expanded		Recov	Recovered after heating		Minimum total wall		Minimum jacket wall		Minimum adhesive wall	
Part number	as sup	as supplied									
ES2000-No.1	5.72	0.225	1.27	0.050	1.20	0.047	0.64	0.025	0.56	0.022	
ES2000-No.2	7.44	0.293	1.65	0.065	1.52	0.060	0.76	0.030	0.76	0.030	
ES2000-No.3	10.85	0.427	2.41	0.095	1.91	0.075	0.89	0.035	1.02	0.040	
ES2000-No.4	17.78	0.700	4.45	0.175	2.41	0.095	1.04	0.041	1.37	0.054	

**Wall thickness will be less if tubing recovery is restricted during shrinkage

Ordering information

Color	Black
Size selection	Consult manufacturer's recommended size selection guidelines.
Standard packaging	Cut pieces. See reverse for information on standard cut lengths.
Marking	Tubing will be marked with the number size (for example, ES-1, ES-2, ES-3, or ES-4).
Ordering description	Specify product name, size, color, and cut length; for example, ES2000-No.2-0-50MM (0=Black).

Specification values

	Property	Unit	Requirement	Method of test
Material	Dimensions	mm (inches)	See reverse	ASTM D 2671
	Longitudinal change	percent	0 to -10	ASTM D 2671
	Tensile strength	psi <i>(MPa)</i>	1500 <i>(10.3)</i> minimum	ASTM D 2671
	Ultimate elongation	percent	250 minimum	ASTM D 2671
	Secant modulus at 2% (expanded)*	psi <i>(MPa)</i>	20,000 <i>(137)</i> minimum	ASTM D 2671
	Heat shock (4 hours at 225°C/ <i>437°F</i>)		No dripping, flowing or cracking of outer jacket	ASTM D 2671
	Dynamic cut through	pounds (kg)	30 <i>(13.6)</i> minimum	ASTM D3032
	Volume resistivity	ohm-cm	1.0 X 10 ¹² minimum	ASTM D 2671
	Flammability		Self-extinguishing	See note below
			within 30 seconds	
Splice performance	Current leakage	microamps	0.25 maximum	See note below
	Room temperature flex test Current leakage	microamps	0.25 maximum	See note below
	Thermal shock Current leakage	microamps	0.25 maximum	See note below
	Low-temperature flexibility Dielectric withstand 1 minute at 1000 V		No breakdown	See note below
	Heat aging			See note below
	Current leakage	microamps	0.25 maximum	
	Fluid immersion Current leakage Swell	microamps percent	0.25 maximum 50 maximum	See note below

Note: Consult Raychem RT-1112 for specific details about test procedures.

*Calculate based on wall thickness of jacket only.

Standard cut lengths

Part number	Standard cut length	Cut length tolerance	
ES2000-No. 1	27 mm, 50 mm, 65 mm	± 1.5 mm	
	1220 mm	± 25.4 mm	
ES2000-No. 2	27 mm, 50 mm, 65 mm	± 1.5 mm	
	1220 mm	± 25.4 mm	
ES2000-No. 3	27 mm, 65 mm, 75 mm	± 1.5 mm	
	1220 mm	± 25.4 mm	
ES2000-No. 4	27 mm, 75 mm, 90 mm	± 1.5 mm	
	1220 mm	± 25.4 mm	

Raychem is a trademark of Tyco Electronics Corporation.

Users should independently evaluate the suitability of the product for their application.

Tyco Electronics Corporation 300 Constitution Drive Menlo Park, CA 94025-1164 USA Tel: (800) 926-2425 (US & Canada) Tel: +1 (650) 361-3860 (All other countries)

Faraday Road Dorcan, Swindon, SN3 5HH United Kingdom Tel: +44 1793 528171 3816 Noborito, Tama-ku Kawasaki, Kanagawa 214-8533 Japan Tel: +81 44 900 5102 Asia Pacific Headquarters 26 Ang Mo Kio, Industrial Park 2 Singapore 569507 Tel: +65 4866 151

All information, including illustrations, is believed to be reliable. Users, however, should independently evaluate the suitability of each product for their application. Tyco Electronics Corporation makes no warranties as to the accuracy or completeness of the information, and disclaims any liability regarding its use. Tyco Electronics Corporation's only obligations are those in the Standard Terms and Conditions of Sale for these products and in no case will Tyco Electronics Corporation be liable for any incidental, indirect, or consequential damages arising from the sale, resale, use, or misuse of the product. Tyco Electronics Corporation's Specifications are subject to change without notice. In addition, Tyco Electronics Corporation reserves the right to make changes in materials or processing without notification to the Buyer which do not affect compliance with any applicable specification.