




REV. 1 8/27/97

COIL: @ 25°C

RESISTANCE 390 OHMS ± 10%

NOMINAL VOLTAGE 12.0 VDC

MUST OPERATE 7.0 VDC

MUST RELEASE 4.0 VDC MAX. 0.63 VDC MIN.

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's

SHOCK 75 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2 MS MAX

RELEASE TIME 4 MS MAX

CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 4/23/97 CK. JERRY 8/27/97

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. TELEDYNE
CUST. NO. ER412D-12A

TYPE PRMAD RELAY

PRMACD-12X