

COIL:

RESISTANCE 675 OHMS ± 20%

NOMINAL VOLTAGE 26.5 VDC

MUST OPERATE 13.5 VDC

MUST RELEASE 1.47 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 100 g's 6 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: \_\_\_\_\_

\_\_\_\_\_

\_\_\_\_\_

CUSTOMER DATA SHEET



CONTACT RATING: 2 AMPS  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 8/7/92 CK. 8/7/92

**COMMUNICATIONS INSTRUMENTS, INC.**

CUST. C. I. I. STD

CUST. NO. \_\_\_\_\_

TYPE "FW" RELAY

FW1101G00