


COIL: @ 25°C
 RESISTANCE 50 OHMS ± 10%
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 2.7 VDC
 MUST RELEASE 1.4 VDC MAX. 0.22 VDC MIN.

ENVIRONMENT
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 75 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C


NOTES: OPERATE TIME 2 MS MAX
RELEASE TIME 4 MS MAX
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR RB 7/10/98 CK. *7/10/98*



CUST. TELEDYNE
 CUST. NO. ER412D-5A

TYPE PRMAD RELAY

PRMACD-5X