




REV. 0

DCO 16707

COIL: @ 25°C
 RESISTANCE _____ 675 OHMS ± 10%
 NOMINAL VOLTAGE _____ 26.5 VDC
 MUST OPERATE _____ 13.5 VDC

 MUST RELEASE _____ 2.3 VDC

ENVIRONMENT:

VIBRATION _____ 10 _____ CPS TO _____ 2000 _____ CPS @ _____ 20 _____ g's


SHOCK _____ 100 _____ g's _____ 6 _____ MS. DURATION

TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: OPERATE & RELEASE 6 MS MAX.

CONTACT BOUNCE 1 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: 2A 28 VDC
 RESISTIVE 100,000 OPERATIONS

DR. PBB. 1/5/01

CK.TLG 1-5-01

CH Technologies
 advanced control electronic solutions

CUST. _____ OPL
 CUST. NO. M5757/10-037 REV. _____

"FW" RELAY

FW1167G06