


REV. 0
DCO 143205

COIL: @ 25°C
 RESISTANCE _____ 50 OHMS ±10%
 NOMINAL VOLTAGE _____ 5.0 VDC
 MUST OPERATE _____ 2.7 VDC

 MUST RELEASE _____ 1.4 VDC MAX, 0.22 VDC MIN.

ENVIRONMENT:
 VIBRATION _____ 10 _____ CPS TO _____ 3000 _____ CPS @ _____ 30 _____ g's
 SHOCK _____ 75 _____ g's _____ 6 _____ MS. DURATION
 TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C
 NOTES: _____ OPERATE TIME 2.0 MS MAX
 _____ RELEASE TIME 4.0 MS MAX
 _____ CONTACT STABILIZATION TIME 2.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: _____ LOW LEVEL TO 1 AMP
 _____ 28 VDC RESISTIVE 100,000 OPERATIONS

DR. BSH 9/12/01 CK. JERRY 9/12/01



CUST. _____ C.I.I.
 CUST. NO. _____ COTS STD. _____ REV. _____

"PRMGAD" RELAY

PRMGACDG-5YW