

Accessories Force Guided Relay SR2M Plug-in

- For Force Guided Relay SR2M Plug-in, pinning 5 mm
- Simple plug-in indicator- and protection modules
- white snap-on marking tags
- RoHS compliant (Directive 2011/65/EU)

Premium socket with screwless terminals for DIN rail mounting

RT 78 72P Premium socket, logical terminal arrangement

- **■** Screwless Clamps
- Mounting of solid wires without tool
- **■** Double Clamps per terminal
- Jumper links for interconnection







Approvals




Technical Data	
Rated voltage / Max. switching voltage	240 / 400 VAC
Rated current	2 x 6A
Dielectric strength	
coil contact circuit	4000 V _{rms}
open contact circuit	1000 V _{rms}
adjacent contact circuit	2500 V _{rms}
Clearance / creepage coil contact circuit	≥ 8 / 8mm
Material group of insulation parts	IIIa
Flammability class UL 94	V-0
Insulation to IEC 60664-1	
Type of insulation coil-contact circuit	reinforced
open contact circuit	functional
adjacent contact circuit	functional
Rated isulation voltage	250 V
Pollution degree	2
Rated voltage system	230 / 400 V
Overvoltage category	IIII
RoHS - Directive 2002/95/EC	compliant
Ambient temperature range	
for mounting/handling	-20+70°C
in operation	-25+70°C
Terminals	screwless
Wire strip length	12 mm





Derating Curve RT7872P





Accessories Force Guided Relay SR2M Plug-in (Continued)

Wire cross section

solid wire

with standard isolation (no oversize isolation) 1x0.75/1/1.5mm²

2x0.75/1.5mm²

2x1.5mm²

stranded wire

1x0.75/1/1.5mm² without bootlace crimp

2x0.75mm² 2x1.5mm²

without bootlace crimp with standard isolation 1x0.75/1.5mm² with bootlace crimp 2x0.75mm²

with bootlace crimp without isolation or min 18 mm long 1x0.75/1.5mm²


For stranded wires with braids 0.05 mm or smaller the use of bootlace crimps is recommended. When using stranded wires without bootlaces crimp the clamp must be opened during insertion.


entitip the damp made be opened daming medition.	
Insertion cycles	A (10)
Max. Insertion Force total	100N
Mounting distance	≥ 0, dense packing
Weight	36 g
Packaging unit	10 pcs


Socket with screwless terminals for DIN rail mounting		
Type		Part Number
RT 78 72P	Premium socket, logical terminals arrangement Socket with screwless terminals, pinning 5 mm for DIN rail mounting	1860200-1


Accessories for RT 78 72P			
Туре		Part Number	
XT 28816	Metal retaining clip, relay height 25.5mm	1887204-1	
RT 17 040	Marking tag	2-1415038-1	
RT 17 0P1	Jumper link, max load 12A	1860211-1	

How to use, Precautions












Accessories Force Guided Relay SR2M Plug-in (Continued)


Socket with screw-type terminals for DIN rail mounting

RT 78 726 Socket with screw-type terminals, logical terminal arrangement

- Din-rail socket with logical setup of connectors (input/output)
- **■** High quality rising clamp terminals
- **■** Captive combination terminals screws
- **■** Jumper bars for interconnection








Approvals

√E VDE 116064, c¶us UL E135149

Technical data	RT 78 726	
Rated voltage / Max. switching voltage	240 / 400VAC	
Rated current	2x6A	
Dielectric strength coil contact circuit	4000 V _{rms}	
open contact circuit	1000 V _{rms}	
adjacent contact circuit	2500 V _{rms}	
Clearance / creepage coil contact circuit	≥ 8 / 8mm	
Material group of insulation parts	Illa	
Flammability class UL 94	V-0	
Insulation to IEC 60664-1		
Type of insulation coil-contact circuit	reinforced	
open contact circuit	functional	
adjacent contact circuit	functional	
Rated isulation voltage	250V	
Pollution degree	2	
Rated voltage system	230 / 400V	
Overvoltage category	IIII	
RoHS - Directive 2002/95/EC	compliant	
Ambient temperature range		
for mounting/handling	-20+70°C	
in operation	-25+70°C	

Derating Curve RT 78726 (SR2M)





Accessories Force Guided Relay SR2M Plug-in (Continued)

Terminals	screw
Terminals screw torque acc. IEC 61984	0.5Nm
Terminals max.	0.7Nm
Wire cross section	
single wire	2 x 2.5 mm ²
fine wire	2 x 2.5 mm ²
with bootlace crimp (DIN 46228/1)	2 x 1.5 mm ²
Insertion cycles	A (10)
Max. Insertion Force total	120 N
Mounting distance	≥ 0, dense packing
Weight	36 g
Packaging unit	10 pcs
single wire fine wire with bootlace crimp (DIN 46228/1) Insertion cycles Max. Insertion Force total Mounting distance Weight	2 x 2.5 mm ² 2 x 1.5 mm ² A (10) 120 N ≥ 0, dense packing 36 g

Socket with screw-type terminals for DIN rail mounting			
Туре		Part Number	
RT 78 726	Socket with screw-type terminals, pinning 5 mm for DIN rail mounting, logical terminal arrangement	6-1415035-1	

Accessories for RT 78 726			
Type		Part Number	
XT 28816	XT 28816 Metal retaining clip, relay		
	height 25.5 mm		
RT 17 040	Marking tag	2-1415038-1	
RT 17 0R8	Jumper bar, max load 12A	1860517-8	
	for connection of up to 8 RT Sockets		

LED- and Protection Modules for RT7872P, RT78726			
Easy insertion	of module	into the socket	
Wiring in parall	el to the c	oil	
Туре			Part Number
PTM TO 0A0	EM09	Protection diode	9-1415036-1
		(standard, A1+,A2-)	
PTM TO OLO	EM01	Protection diode(A1-,A2+)	1415037-1
LED			
PTM L0 024	EM18	red LED 624VDC w.	5-1415036-1
		prot.diode (std, A1+, A2)	
PTM G0 024	EM12	green LED 624VDC w.	2-1415036-1
		prot.diode (std, A1+, A2-)	
PTM L1 024	EM08	red LED 624 VDC w.	8-1415036-1
		prot. Diode (A1-, A2+)	
PTM L0 060	EM16	red LED 2460VDC w.	5-1415539-3
		prot. Diode (std, A1+, A2-)	
PTM G0 060	EM25	green LED 2460VDC w.	7-1415539-7
		prot.diode (std, A1+, A2-)	
PTM L0 110	EM19	red LED 60110VDC w.	2-1415392-1
		prot. Diode (A1+, A2-)	

Marking tags

- White marking area 15.5 x 6mm
- Snaps on socket in up to 4 positions

