


COIL: @ +25° C
 RESISTANCE 27 OHMS ± 10%
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 2.7 VDC
 MUST RELEASE 1.65 VDC MAX .29 VDC MIN

ENVIRONMENT:
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's
 SHOCK 100 g's 6 ± 1 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 4 MS MAX
CONTACT STABILIZATION 2 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 9/21/94 CK. 9/21/94

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. QPL
 CUST. NO. M39016/6-135P

TYPE 'HFW' RELAY

HFW1131L01P