


COIL: @ +25 °C  
 RESISTANCE 160 OHMS ± 10%  
 NOMINAL VOLTAGE 12.0 VDC  
 MUST OPERATE 7.2 VDC  
 MUST RELEASE 0.7 VDC

ENVIRONMENT:  
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 100 g's 6 ± 1 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: MAXIMUM TRANSIENT SUPPRESSED VOLTAGE  
OF -24 VDC WITH BIFILAR COIL

**CUSTOMER DATA SHEET**



CONTACT RATING: LOW LEVEL TO 2A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 11/1/91 CK. *V. J. [Signature]*



CUST. QPL  
 CUST. NO. M39016/22-016M

TYPE "HMB" RELAY

**HMB1201G01M**