




REV. 0
DCO 143419


COIL: @ 25°C
RESISTANCE 100 OHMS $\pm$ 10%
NOMINAL VOLTAGE 5.0 VDC
MUST OPERATE 2.6 VDC
MUST RELEASE 1.4 VDC MAX, 0.23 VDC MIN.

ENVIRONMENT:

VIBRATION 10 Hz TO 3000 Hz @ 30 g's
SHOCK 75 g's 6 MS. DURATION
TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX.
RELEASE TIME 7.5 MS MAX.
CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 01/21/02

CII Technologies
advanced control electronic solutions

CUST. CII
CUST. NO. COTS STD REV.
"PRMSD" RELAY

PRMSCDF - 5XW