




COIL:

RESISTANCE 98 OHMS $\pm$ 10%

NOMINAL VOLTAGE 6.0 VDC

MUST OPERATE 4.2 VDC

MUST RELEASE _____

ENVIRONMENT:

VIBRATION 10 CPS TO 500 CPS @ 10 g's


SHOCK 30 g's 6 MS. DURATION

TEMPERATURE -55 °C TO +85 °C

NOTES: OPERATE TIME 4.0 MS MAX

RELEASE TIME 6.0 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO

1A 28 VDC RESISTIVE 100,000

OPERATIONS

DR. R.B. 4/24/98 (CK) 9/24/98

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. C. I. I. STD

CUST. NO. _____

TYPE "HMD" RELAY

HMD2-6B