


The PT8510 can operate from an unregulated 14.5 to 40 VDC power supply while providing an output signal that is proportional to the linear movement of its measuring cable. The PT8510 has a maximum measurement range up to 60" and has 4 output signal options to choose from: 0...10, 0...5, -10...+10 and -5...+5 Vdc.

As a member of our innovative family of NEMA-4 rated cable-extension transducers, the PT8510 offers numerous benefits. It installs in minutes, fits into areas unsuited for rod-type measurement devices, and works without perfectly parallel alignment.

**Output Signal** 



\*Also Available: 0...5, -5...+5, -10...+10 Vdc

# PT8510 Cable Actuated Sensor Heavy Industrial • 0...5, 0...10 Vdc

Absolute Linear Position to 60 inches (1524 mm) Aluminum or Stainless Steel Enclosure Options VLS Option to Prevent Free-Release Damage IP68 • NEMA 6 Protection

# General

Full Stroke Range	0-2 to 0-60 inches
Options	
Output Signal	05, 010, -5+5, -10+10 VDC
Accuracy	$\pm$ 1.00% to $\pm$ 0.15% full stroke (see ordering information)
Repeatability	± 0.05% full stroke
Resolution	essentially infinite
Measuring Cable	nylon-coated stainless steel or thermoplastic
Enclosure Material	powder-painted aluminum or stainless steel
Sensor	plastic-hybrid precision potentiometer
Potentiometer Cycle Life	see ordering information
Maximum Retraction Acceleration	see ordering information
Weight	3 lbs. (6 lbs.) max.


# Electrical

- Input Voltage Input Current Output Impedance Maximum Load Zero and Span Adjustment
- see ordering information 10 mA maximum 1000 ohms 5000 ohms see ordering information

# Environmental


Enclosure	NEMA 4/4X/6, IP 67/68
Operating Temperature	-40° to 200°F (-40° to 90°C)
Vibration	up to 10 g to 2000 Hz maximum

# **Outline Drawing:**



note: \*tolerance = +.005 -.001 [+.13 -.03] \*\*tolerance = +.005 -.005 [+.13 -.13]

# **Ordering Information**



#### Sample Model Number:

PT8510 - 0030 - 111 - 1110								
<ul> <li>() range:</li> <li>() enclosure/cable tension:</li> <li>() measuring cable:</li> <li>() output signal:</li> <li>() electrical connection:</li> <li>() cable guide option:</li> </ul>	30 inches aluminum/standard (9 oz.) .034 nylon-coated stainless 010 vdc 6-pin plastic connector standard nylon cable guide							

#### Full Stroke Range:

R order code:	0002	0005	0010	001	5	0020		0025	0030	0040	0050	0060
full stroke range, min:	2 in.	5 in.	10 in.	15 ii	ı <b>.</b>	20 in.	:	25 in.	30 in.	40 in.	50 in.	60 in.
accuracy (% of f.s.):	1.00%	1.00%	0.18%	0.18	%	0.18%	-	0.18%	0.18%	0.15%	0.15%	0.15%
potentiometer cycle life*:	2.5 x 10 <sup>6</sup>	2.5 x 10 <sup>6</sup>	5 x 10 <sup>5</sup>	5 x 1	ן 5כ	5 x 10 <sup>5</sup>	:	5 x 10 <sup>5</sup>	5 x 10 <sup>5</sup>	2.5 x 10 <sup>5</sup>	2.5 x 10 <sup>5</sup>	2.5 x 10 <sup>5</sup>

\*-1 cycle is defined as the travel of the measuring cable from full retraction to full extension and back to full retraction


## **Enclosure Material and Measuring Cable Tension:**

(A) order code:	1	I	5	2	3	(	6	4	8	7	,	9
enclosure:		aluı	ninum			303 st	ainless			316 sta	inless	
cable tension:	stan	dard me	dium	high	standard	med	lium	high	standard	med	ium	high
max. acceleration:	15	g 2	5 g	40 g	бg	12	g	18 g	6 g	12	g	18 g
		Range:	2 in.	5 in.	10 in.	15 in.	20 in.	25 in.	30 in.	40 in.	50 in.	60 in.
	(	Standard:	39 oz.	16 oz.	39 oz.	26 oz.	20 oz.	16 oz.	13 oz.	20 oz.	16 oz.	13 oz.
cable tension option	٦.	Medium:	65 oz.	26 oz.	65 oz.	43 oz.	33 oz.	26 oz.	22 oz.	33 oz.	26 oz.	22 oz.
specifications	l	High:	116 oz.	47 oz.	116 oz.	77 oz.	60 oz.	47 oz.	40 oz.	60 oz.	47 oz.	40 oz.
										ter	nsion tolera	nce: ± 50%


## Measuring Cable:

<b>B</b> _order code:	1	2	3	4
cable construction:	Ø.034-inch nylon-coated stainless steel rope	Ø.047-inch bare stainless steel rope	Ø.058-inch PVC jacketed vectra fiber rope	Ø.031-inch bare stainless steel rope
available ranges:	all ranges	5, 15, 20, 25, 30-inch only	thru 30 inches only	40, 50, 60-inch only
general use:	indoor	outdoor, debris, high temperature	high voltage or magnetic field	outdoor, debris, high temperature


## **Output Signals:**



#### **Electrical Connection:**



\*-Test pressure: 100 feet [30 meters] H2O (40 PSID); Test Medium: Air; Duration: 2 hours. \*\* -Applies to stainless steel enclosure only.




### \*note: all ranges up to 25 inches only

**Cable Guide Options:** 

#### Output Signal Selection (does not apply to -5...+5 and -10...+10 VDC options)

The output signal direction can be reversed at any time by simply changing the dip-switch settings found on the internal signal board. After the settings have been changed, adjustment of the Zero and Span trimpots will be required to precisely match signal values to the beginning and end points of the stroke.



# VLS Option - Free Release Protection

The patented Celesco Velocity Limiting System (VLS) is an option for PT8000 Series cable extension transducers that limits cable retraction to a safe 40 to 55 inches per second.

The VLS option prevents the measuring cable from ever reaching a damaging velocity during an accidental free release. This option is ideal for mobile applications that require frequent cable disconnection and reconnection. It prevents expensive unscheduled downtime due to accidental cable mishandling or attachment failure.

VLS is NOT available for medium and high cable tension options or 2, 5 and 15-inch stroke ranges.

### How to Configure Model Number for VLS

VLS8510-			6	<u> </u>				<b>0</b>
	0015		1			1	1	0
	0020		2			2	2	1
	0025		3			3	3	3
	0030		4			4	4	
	0040					5	5	
	0050					6	6	
	0060					7	7	
= available option	= available options**					8		
creating VLS model num	ber (example):							
1. select PT8420 mode	2		P	Г8510	)-006(	0-11	1-1	110
2. remove "PT" from th	ber	r 🕅 🕅 🕅 🕅 🕅 🕅						
3. add "VLS"		VL	.S +	8510	)-006(	0-11	1-1	110
4. completed model n	umber!		VL	S8510	)-006(	0-11	1-1	110

\*\*Note: please contact factory for a solution to options not supported.

#### **NORTH AMERICA**

Measurement Specialties, Inc., a TE Connectivity company 20630 Plummer Street Chatsworth, CA 91311 Tel +1 800 423 5483 Tel +1 818 701 2750 Fax +1 818 701 2799 info@celesco.com

#### TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.

PT8510 12/01/2015